

Electronic 3-point internal micrometers set

interchangeable measuring head set

Mitutoyo

Application:

For measuring through-bores and for blind holes and short centring shoulders.

Execution:

- Titanium-coated pins
- Cone: Tungsten carbide
- LCD display, digit size 11 mm
- 330° rotating display unit allows easy reading at any working angle
- GO/NG tolerance judgement function
- Each set includes a measuring instrument with replaceable measuring heads in the specified size
- 3-point internal measuring instrument with spring mechanism

Advantage:

- Measurement values can easily be read from the large LCD display
- A function lock protects against changes to the setting by unauthorised users

Delivery:

Including box, setting key, 1x battery, factory test certificate (basic units only – factory certificate for setting rings is not included)



Art. no.	32017 778
Brand	MITUTOYO
Manufacturer Part Number	568-930
Min./max. length measuring range	1-2 in
Data transmission type	DIGIMATIC
Digit increment	0.00005 in
Adjusting ring diameter	1.2 inch, 1.6 inch
With ABS function	Yes
Number of rechargeable batteries/batteries	1 PCS
Battery designation	1,5 V SR44
Design	Metric, Imperial
Digit height	11 mm
Calibration Group	I
Gross Weight	3.360 kg
Product Group	3MA

EAN

4946368636771