

## Solid carbide quarter circle milling cutter

Concave

**ORION**<sup>®</sup>

### Application:

Quarter circle milling cutter for machining complex forms, e.g. bore radii in materials up to 1300 N/mm<sup>2</sup>.



### Execution:

- Straight shank pursuant to DIN 1636 HA
- Tolerance R = +/- 0.01 mm

<b>Art. no.</b>	<b>16711 925</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	16711925
<b>Cutting material</b>	SC
<b>Surface</b>	TiAlN
<b>Type</b>	N
<b>Number of cutting edges</b>	4 PCS
<b>Tool holding device</b>	HA parallel shank
<b>Radius</b>	2.5 mm
<b>Min. cutting edge diameter</b>	7 mm
<b>Max. cutting edge diameter</b>	12 mm
<b>Length</b>	75 mm
<b>Shank diameter</b>	12 mm
<b>fz steel 1000</b>	0.028 mm
<b>Gross Weight</b>	0.111 kg
<b>Product Group</b>	150

### EAN

4039247574117