



# Actinic BL TL(-K) / TL-D(-K)

## Actinic BL TL 40W/10 SLV/25

With an optimized spectrum matching the eye sensitivity of the housefly, Actinic BL TL(-K)/TL-D(-K)/TL-E/PL-S and PL-L lamps are perfect for attracting insects. They have virtually no UV-B output, and so are perfectly safe. What's more, with the lowest mercury content in the industry and being 100% lead-free, these lamps represent a very good environmental choice. Furthermore, the availability of a wide range of form factors (straight (T5, T8, T12), circular (TL-E) and compact (PL-S/PL-L)) and wattages enables you to make all kinds of designs for your electronic fly killers

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

### Product data


General Information		Voltage (Nom)	
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	101 V	
Light Technical		Mechanical and Housing	
Color Code	10	Bulb Shape	T12 [38 mm (T12)]
Color Designation	Actinic	Approval and Application	
Chromaticity Coordinate X (Nom)	220	Mercury (Hg) Content (Nom)	13.0 mg
Chromaticity Coordinate Y (Nom)	205	Product Data	
Operating and Electrical		Full product code	871150026026000
Power Consumption	39 W	Order product name	Actinic BL TL 40W/10 SLV/25
Lamp Current (Nom)	0.43 A	Order code	928011301020
Voltage (Nom)	101 V	Navigator - Quantity Per Pack	1

## Actinic BL TL(-K) / TL-D(-K)

Numerator - Packs per outer box	25
Material number (12NC)	928011301020
Full product name	Actinic BL TL 40W/10 SLV/25


EAN/UPC - Case	8711500260277
----------------	---------------

### Dimensional drawing



Product	D (max)	A (max)	B	C (max)
Actinic BL TL 40W/10 SLV/25	37.25 mm	1,198.4 mm	1,205.4 mm	1,212.4 mm

### Photometric data



Spectral Power Distribution Colour - Actinic BL TL 40W/10 SLV/25

