

# Twin RG6U Coaxial Cable

pro-POWER

RoHS  
Compliant



## Specifications:

### Designed of cable

Inner conductor	: Single Steel Copper (1.02mm ±0.01mm)
Insulation	: Air space PE
Size of Insulation	: 4.7mm ±0.1mm
Aluminate	: Aluminate outside
Braiding	: 16 × 4/0.12 ±0.003mm Al/Mg
Jacket	: PVC
Colour	: Black
Size	: 6.5 + 6.5 ±0.2mm
Wall Thickness	: 0.7mm

### Electric data at 20°C

Conductor Resistance	: ≤117Ω/kM
Insulation Resistance	: ≥5,000M Ω × kM
Testing voltage	: 50Hz 1Min wire/wire 50Hz 1min = 1.5kV
Impedance	: 75 ±3Ω at 200Mhz

Permissible temperature : -10°C to 60°C

### ATT

Frequence	50	100	200	800	1000
ATT dB/100m	11	18	20.5	30.5	33.8

## Part Number Table

Description	Part Number
Twin RG6U Coaxial Cable Black, 100m	RG6UTWINBLK

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com  
www.farnell.com  
www.newark.com  
www.cpc.co.uk

pro-POWER