# Straight FME Plug to SMA Jack Adapter

**multicomp** PRO

**RoHS Compliant**

## Specifications

| | | |
|---|---|---|
| Frequency Range | : DC-900 MHz |
| Nominal Impedance | : 50Ω |
| Working Voltage | : 500 Volts Max. |
| Proof Voltage | : 1000 Volts |
| Vswr | : 1.3 |
| Bodies | : Brass per JIS-C3604 |
| Centre Contact | : Beryllium copper per ASTM B196 UNS C17300 |
| Insulation | : PTFE Per ASTM D1457 and ASTM D1710 |
| Operating Temperature Range | : -55°C to +125°C |

## Diagram



4 STAMPING

1/4"-36UNS

M8XP0.75
9.5(.374) HEX.

12.7(.500)

20.3±0.5(.799±.020)

(0 +.039 −0)
0 +1 −0

| No | Description | Material | Qty. | Finish |
|---|---|---|---|---|
| 1 | Insulation | PTFE | 1 | None |
| 2 | Centre Contact | Beryllium Copper | | Gold |
| 3 | Insulation | PTFE | | None |
| 4 | Body | Brass | | Nickel 100µ″ Min. |

Dimensions : Millimetres (Inches)

## Part Number Table

| Description | Part Number |
|---|---|
| Straight FME Plug to SMA Jack Adapter | MP-R23-004-00-002621000 |

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

**multicomp** PRO

Page <1>

06/07/21   V1.0