

ROCKER SWITCHES

PRODUCT NUMBER 1921.1101



TECHNICAL DATA

Product number	1921.1101						
Business unit	Switches, Sensors & Controls						
Product Manager	-						
Product family	Rocker switches						
Actuation type	direct						
Packing unit	300						
Weight	3.500 g						
ROHS conform	yes						
Output	catalog before 2009 / catalog						
Switching function	ON / OFF switch (SPST)						
Material fixed contact	Cu silver-plated						
Number of poles	1 - pole						
connections	Quick-connect terminal, 4.8 x 0.8						
Mechanical life endurance	75E3						
Rating IEC	6 (2) A 250 V AC 4 (1) A 250 V AC 5E4						
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm						
Insulation resistance (new condition)	> 100 (500 V DC) MOhm						
Voltage strength at 250 V	<table> <tr> <td>→ function insulation / basic insulation</td> <td>1 500 V</td> </tr> <tr> <td>→ reinforced insulation</td> <td>3 000 V</td> </tr> <tr> <td>→ small contact distance</td> <td>500 V</td> </tr> </table>	→ function insulation / basic insulation	1 500 V	→ reinforced insulation	3 000 V	→ small contact distance	500 V
→ function insulation / basic insulation	1 500 V						
→ reinforced insulation	3 000 V						
→ small contact distance	500 V						
Proof tracking	250 PTI						
Insulation spacing	acc. to EN 61058 for reinforced or double insulation						
Protection type	<table> <tr> <td>→ Connection</td> <td>IP 40</td> </tr> <tr> <td>→ Actuator</td> <td>IP 40</td> </tr> </table>	→ Connection	IP 40	→ Actuator	IP 40		
→ Connection	IP 40						
→ Actuator	IP 40						
Ambient temperature	→ connection side -20 °C ... +85 °C						
Ambient temperature	→ Actuation side min. -20 °C ... +55 °C						
Storage temperature	-40 °C ... +80 °C						

Flammability	UL 94 V-2
Glow wire test temperature	850 °C
Actuators and additional actuators	rocker: PA, white
Housing description	housing: PA, white
Connection surface	→ bearing connection silver plated → external connection silver plated
Contact material	Ag
Contact distance	≥ 3 mm
Contact type	lifting contact
Plug force of the terminals	≤ 80 N
Operating force	2 - 5 N
Approval marks	cULus / ENEC 05
Suitable for appliances of protection class	II
Type of fastening	Snap fastening
Degree of pollution	3

Technical changes reserved. Dimensions are not binding.

Detailed specifications available on request.

Marquardt GmbH · Schloss-Straße 16 · 78604 Rietheim-Weilheim · Germany
 Phone: +49 (0) 7424 / 99-0 · Fax: +49 (0) 7424 / 99-2399 · www.marquardt.com · marquardt@marquardt.de