

## MZE clamping sleeves

For sleeve tensioning spindles



### Application:


For inspection, light turning tasks, for grinding and balancing.

### Execution:

- For accommodation between points.
- An even and cylindrical tensioning force is achieved with the alternately slotted spreader sleeves.
- Hardened and ground.
- Concentricity tolerance 0.01 mm.
- Individual clamping sleeves, no. 22301.

### Delivery:

1x clamping sleeve 8 mm.



<b>Art. no.</b>	<b>22301 024</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	315050
<b>Outer diameter</b>	24 mm
<b>Expansion</b>	2 mm
<b>Clamping mandrel length</b>	80 mm
<b>Gross Weight</b>	0.297 kg
<b>Product Group</b>	205

### EAN

4019208070773