

## Electronic 3-point internal micrometers set

Complete set

Mitutoyo

### Application:

For measuring through-bores and for blind holes and short centring shoulders.

### Execution:

- Each set contains one measuring instrument incl. measuring head in specified size.
- Titanium-coated pins
- Cone: Tungsten carbide
- LCD display, digit size 11 mm
- 330° rotating display unit allows easy reading at any working angle
- GO/NG tolerance judgement function
- Each set includes a measuring instrument with replaceable measuring heads in the specified size
- 3-point internal measuring instrument with spring mechanism

### Advantage:

- Measurement values can easily be read from the large LCD display
- A function lock protects against changes to the setting by unauthorised users

### Delivery:

Includes box, adjustment wrench, 1 battery, factory test certificate



<b>Art. no.</b>	<b>32017 788</b>
<b>Brand</b>	MITUTOYO
<b>Manufacturer Part Number</b>	568-968
<b>Min./max. length measuring range</b>	2-3 in
<b>Data transmission type</b>	DIGIMATIC
<b>Digit increment</b>	0.00005 in
<b>Adjusting ring diameter</b>	2.5 inch
<b>With ABS function</b>	Yes
<b>Number of rechargeable batteries/batteries</b>	2 PCS
<b>Battery designation</b>	1,5 V SR44
<b>Design</b>	Metric, Imperial
<b>Digit height</b>	11 mm
<b>Calibration Group</b>	I
<b>Gross Weight</b>	6.110 kg
<b>Product Group</b>	3MA

### EAN

4946368636870