

G1 G2 G3


G Series Finishing Tools
Outils de Finition, Série "G"
Werkzeuge zur Oberflächenbearbeitung der Baureihe G
Herramientas de Acabado - Serie G
Utensili per la Finitura - Serie G

Angle grinders
 Meuleuses d'angle
 Winkelschleifmaschinen
 Amoladoras angulares
 Smerigliatrici ad angolo



G1A200PG4M

G3A120PP95



Specifications at 90 psi – Caractéristiques à 6,2 bar – Technische Daten bezogen auf 6,2 bar – Especificaciones a 6,2 bar – Caratteristiche a 6,2 bar

Ref.	kWatt kW	1 min. rpm			kg					
										mm
STANDARD MODELS - MODÈLES STANDARDS - STANDARDMODELLE - MODELOS ESTÁNDAR - MODELLI STANDARD										
G1A120PG4M	0.30	12 000	Ø 6 Erickson	–	0.50	152	76	1/4	10	
G1A200PG4M	0.30	20 000	Ø 6 Erickson	–	0.50	152	76	1/4	10	
G1A200PP63	0.30	20 000	–	Ø 75 - Type 27	0.60	152	48	1/4	10	
G1A200PH63	0.30	20 000	–	Ø 75 - Type 1	0.60	152	48	1/4	10	
G2A100PG4M	0.60	10 000	Ø 6 Erickson	–	1.00	197	76	1/4	10	
G2A120PG4M	0.60	12 000	Ø 6 Erickson	–	1.00	197	76	1/4	10	
G2A120PP945	0.60	12 000	–	Ø 115 - Type 27	1.45	197	60	1/4	10	
G2A120PP95	0.60	12 000	–	Ø 125 - Type 27	1.63	197	60	1/4	10	
G2A120PP74	0.60	12 000	–	Ø 100 - Type 27	1.36	197	64	1/4	10	
G2A150PP74	0.60	15 000	–	Ø 100 - Type 27	1.36	197	64	1/4	10	
G2A180PG4M	0.60	18 000	Ø 6 Erickson	–	1.00	197	76	1/4	10	
G2A180PP63	0.60	18 000	–	Ø 75 - Type 27	1.40	197	64	1/4	10	
G3A120PP945	1.00	12 000	–	Ø 115 - Type 27	2.00	244	92	3/8	13	
G3A120PP95	1.00	12 000	–	Ø 125 - Type 27	2.10	244	92	3/8	13	
G3A100PP96	1.00	10 000	–	Ø 150 - Type 27	2.20	244	92	3/8	13	
G3A120PP945A (1)	1.00	12 000	–	Ø 115 - Type 27	2.10	244	92	3/8	13	
G3A120PP95A (1)	1.00	12 000	–	Ø 125 - Type 27	2.20	244	92	3/8	13	
G3A100PP96A (1)	1.00	10 000	–	Ø 150 - Type 27	2.30	244	92	3/8	13	
EXTENDED MODELS - MODÈLES LONGS - VERLÄNGERTE MODELLE - MODELOS EXTENDIDAS - MODELLI PROLUNGATI										
G2E135PG4M	0.60	13 500	Ø 6 Erickson	–	1.10	264	76	1/4	10	
G2E135PP74	0.60	13 500	–	Ø 100 - Type 27	1.40	264	67	1/4	10	
G2L100PP96	0.60	10 000	–	Ø 150 - Type 27	2.00	321	60	1/4	10	

(1) **Fitted with autobalancer** – Also available with anti-vibration dead handle; add "V" to model no. (e.g. G3A100PP96AV).
Système d'auto-équilibrage en standard – Egalement disponible avec poignée auxiliaire anti vibration; ajouter "V" à la référence (exemple G3A100PP96AV).
Serienmäßig mit Vibrationsdämpfung – Lieferbar auch mit vibrationsdämpfendem Handgriff (ergänzen Sie die Modell-Nr. mit einem "V", z. B. G3A100PP96AV).
Con sistema de autoequilibrado – También disponible con empuñadura auxiliar anti vibración; añadir "V" a la referencia (ejemplo G3A100PP96AV).
Montato con autobilanciamento – Disponibile anche con imp. ausiliaria anti-vibrazione: aggiungere la lettera "V" al codice del modello (es. G3A100PP96AV).

Angle sanders
 Ponceuses d'angle
 Winkelschmirgelmaschinen
 Lijadoras angulares
 Levigatrici ad angolo



G1A200PS812



See our accessories catalogue for belts.
 Bandes: voir notre catalogue accessoires.
 Schleifbänder finden Sie in unserem
 Zubehörkatalog.
 Ver nuestro catálogo de accesorios para las
 lijas de banda.
 Vedere nostro catalogo accessori per i nastri.

Specifications at 90 psi – Caractéristiques à 6,2 bar – Technische Daten bezogen auf 6,2 bar – Especificaciones a 6,2 bar – Caratteristiche a 6,2 bar

Ref.	kWatt kW	1 min. rpm			kg					
										mm
ANGLE SANDERS - PONCEUSES D'ANGLE - WINKELSCHLEIFMASCHINEN - LIJADORAS ANGULARES - LEVIGATRICI AD ANGOLO										
G1A120PS4M	0.30	12 000	1/4"-20	–	0.50	156	76	1/4	10	
G1A200PS4M	0.30	20 000	1/4"-20	–	0.50	156	76	1/4	10	
G2L100PS10	0.60	10 000	5/8"-11	–	1.80	321	83	1/4	10	
BELT SANDERS - PONCEUSES A BANDE - BANDSCHLEIFMASCHINEN - LIJADORAS DE BANDA - LEVIGATRICI A NASTRO										
G1A120PS812	0.30	12 000	–	12.7 x 305	0.54	273	–	1/4	10	
G1A120PS418	0.30	12 000	–	6.35 x 457	0.54	356	–	1/4	10	
G1A200PS812	0.30	20 000	–	12.7 x 305	0.54	273	–	1/4	10	
WIRE BRUSH TOOL - BROSSEUSE - BÜRSTENSCHLEIFMASCHINE - CEPILLADORA - SPAZZOLATRICI										
G2A090PP9	0.60	9 000	M14	–	1.80	197	83	1/4	10	