




DIN 6314



Brida plana
Plain clamp
Bride droite
Flange plano

Acero C45
Steel C45
Acier C45
Aço C45

Acabado: Epoxi gris
Surface: Grey powder coated
Finition: Peinture epoxy grise
Acabamento: Epóxi cinzento

* Medidas fuera de norma DIN.
* Dimensions outside DIN standard.
* Dimensions hors norme DIN.
* Medidas fora da norma DIN.

Ref.	B	L	M	A	B1	B2	E	E1	gr.
6314-7-50	7	50	M6	10	20	8	10	20	60
6314-9-60	9	60	M8	12	25	10	13	22	110
6314-11-80	11	80	M10	15	30	12	15	30	220
6314-14-80	14	80*	M12 M14	20	40	14	21	30	400
6314-14-100	14	100	M12 M14	20	40	14	21	40	490
6314-14-125	14	125	M12 M14	20	40	14	21	50	640
6314-18-100	18	100*	M16 M18	25	50	18	26	40	850
6314-18-125	18	125	M16 M18	25	50	18	26	45	1.000
6314-18-160	18	160	M16 M18	25	50	18	26	65	1.270
6314-22-160	22	160	M20 M22	30	60	22	30	60	1.830
6314-22-200	22	200	M20 M22	30	60	22	30	80	2.290
6314-22-250	22	250*	M20 M22	30	60	22	30	100	3.000
6314-26-160	26	160*	M24	30	70	26	35	60	2.500
6314-26-200	26	200	M24	30	70	26	35	80	2.650
6314-26-250	26	250	M24	30	70	26	35	105	3.850
6314-34-250	34	250	M30	40	80	34	45	100	5.000
6314-34-315	34	315	M30	50	80	34	45	130	7.800
6314-43-400	43*	400*	M36 M42	60	100	43	100	150	18.000

