

# Amphenol®



## Amphenol® Tru-Loc® Rugged Environment Connector featuring RADSOK® Contacts

Amphenol Industrial Products Group introduces a connection system family with 1.5 mm socket contacts featuring Amphenol's exclusive RADSOK® contact system. The new Tru-Loc connector series is designed to perform in demanding environments, such as under valve covers on diesel engines and in high vibration sensor applications.

Tru-Loc features a molded thermoplastic main plug body with secondary latch and a fluoroelastomer main joint seal that is resistant to many fluids, including diesel fuel.

The Tru-Loc series includes 2-way, 4-way, and 6-way inline plugs and receptacles. Our engineering team can also design this series to mate to a device, sensor, fuel injector, splitter, pass through connector, and more. Special backshells can be designed for the 6-way series, and we can meet 150°C temperatures upon request. These connection systems are RoHS compliant and seal to IP67 when mated. They are rated for high vibrations at 32 Grms.

### Features:

- 2, 4, or 6 pin connector with 1.5mm RADSOK® featured contacts
- Plug body with secondary latch
- Fluoroelastomer main joint seal and silicone rubber wire seals to support IP67 rating
- Dielectric withstanding voltage is 1600 Vac RMS
- 13 Amp current rating
- Insulation resistance can meet 100 M Ohms
- Matting force less then 70N
- Contact retention between 60~80N
- Operating temperature can meet -40°C to +125°C, 100 cycles, 1 hour per cycle
- Durability is 20 mating cycles

[www.amphenol-industrial.com](http://www.amphenol-industrial.com)



<b>Material Specification</b>	
Plug with RADSOK® Socket Contacts	
Plug Body	Nylon
Wire Seal	Silicone
Main Joint Seal	Fluoroelastomer
Socket Contact	Copper Alloy w/ Stainless Steel Hood
Receptacle with Pin Contacts	
Receptacle Body	Copper Alloy
Pin Contact	Copper Alloy

<b>Electrical Specifications</b>	
Dielectric Withstanding Voltage (Test Voltage)	1600 Vac RMS
Current Rating	13 amp (DC) (16 AWG Cable)
Insulation Resistance	100 M Ohms

<b>Mechanical Specifications</b>	
Connector Mating Force	<70 N (15.7 lb)
Contact Retention	Primary Only: 80 N (18.0 lb) Secondary Only: 60 N (13.5 lb)
Vibration	32 g RMS
Operating Temperature Range	-40°/+125°C, 100 cycles, 1 hour per cycle
Ingress Protection	IP67
Durability (Mating Cycle)	20 cycles

<b>AIPG Part Number</b>	<b>Description</b>	<b>Additional Information</b>
10-838275-000	2way Plug (Plug Body, Locking Collar, and Main Joint Seal)	
10-707003-002	4way plug (Plug Body, Locking Collar, and Main Joint Seal)	
10-707508-02X(X: A,B,C,D)	6way plug (Plug Body, Locking Collar, and Main Joint Seal)	4 indexes available
10-707516-001	2way receptacle	
10-707517-001	4way receptacle	
10-707509-00X( X: A,B,C,D)	6way receptacle	4 indexes available
10-838137-00D	Wire seal (silicone)	To be used with insulated wires with insulation between 1.2-2.1 mm.
10-838351-002	Stamped and formed female socket, Au+PdNi plating	Crimps to wire from 0.8-1.3 sq. mm
10-707515-002	Stamped and formed male pin, Au+ PdNi plating	Crimps to wire from 0.8-1.3 sq. mm
10-707515-0M2	Machined male pin, Au+PaNi plating	Crimps to wire from 0.8-1.3 sq. mm

- \* Socket Contacts are available on reels of 4,000 pieces
- \* For Crimp Information please contact factory
- \* Cable seals are sold separately and must be used in all cavities and on both sides of the connection system



For additional information on the Amphe-Power® family of connectors with RADSOK® Technology, please ask for our RADSOK® Catalog (SL-391) or download it from the Catalogs section of our website.

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

For further information on your individual application requirements, contact: Amphenol Corporation

North America:  
Amphenol Industrial Operations  
180 N. Freeport Drive, Plant 4  
Nogales, AZ 85621  
Tel: (520) 285-5130  
Fax: (520) 285-5134

Europe:  
Amphenol Industrial Operations Europe  
Via Barbaiana 5  
1-20020 Lainate (MI) Italy  
Tel: +39 02 93254.204  
Fax: +39 02 93254.444

Middle East:  
Amphenol Middle East Enterprises FZE  
Office C-37 PO Box 21107  
Ajman Free Zone, UAE  
Tel: +9716-7422494  
Fax: +9716-7422941  
Email: ameeffe@eim.ae

Asia:  
Amphenol Technology Shenzhen Ltd  
Block 5 Fuan 2nd Industrial Park  
Dayang Rd, Fuyong Baoan  
Baoan, Shenzhen, China 518103  
Tel: +86 755 2881 8389  
Fax: +86 755 2991 8310  
Email: enquiry@amphenol-aio.com

Email: rpdrzzini@amphenol-aio.com

Email: info@amphenol-aio.com