


## Screwless Terminal Blocks

- 1-36 poles 5, 5.08mm pitch
- 1-24 poles 7.5, 7.62mm pitch
- 1-18 poles 10, 10.16mm pitch
- Easily breakable to desired number of poles, end walls available on request
- Moulded in grey UL94-V0 flame retardant PA
- 0.5-1.5mm<sup>2</sup> (30-16AWG) solid & stranded cable
- Guided pin alignment
- Anti solder wicking
- Spacers in 2.5, 2.54, 5 & 5.08mm available
- Full customisation, produced from 1 pole units which can be pre-assembled to individual requirements
- Available without actuators (screwdriver operation) add suffix /W
-  approved

SPECIFICATION	5mm, 5.08mm	7.5mm, 7.62mm	10mm, 10.16mm
Rating	10A/250V	10A/500V	10A/630V
UL	10A/300V	10A/300V	10A/300V
VDE&IMQ	10A/250V	10A/750V	10A/750V
Dielectric strength	≥2kV	≥2.5kV	≥3kV
Impulse withstand voltage	4kV	6kV	6kV
Working temperature	110°C		
Moulding	UL94-V0 flame retardant PA		
Pin/terminal	Copper alloy, Ni & Sn		
Rising Clamp	Inox steel		
Recommended PCB hole	ø1.1mm		

### 5.08mm

### 5.08mm

TYPE NO.	POLES	LENGTH
CSTBV2/1	1	6.6mm
CSTBV2/2	2	11.7mm
CSTBV2/3	3	16.7mm
CSTBV2/4	4	21.8mm
CSTBV2/5	5	26.9mm
CSTBV2/6	6	32mm
CSTBV2/7	7	37.1mm
CSTBV2/8	8	42.1mm
CSTBV2/9	9	47.2mm
CSTBV2/10	10	52.3mm
CSTBV2/11	11	57.4mm
CSTBV2/12	12	62.5mm
CSTBV2/36	36	184.4mm



CSTBV2

