



SIMATIC S7-300, SIGNAL. MODULE FOR 3 SSI SENSORS FOR READ-IN OF POSITIONING VALUE WITH 2 FREEZE INPUTS , 1 X 20 PIN, SUPPORTS ISOCHRON MODE

Figure similar

Supply voltage	
Load voltage L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
Input current	
from load voltage L+ (without load), max.	100 mA
from backplane bus 5 V DC, max.	160 mA
24 V encoder supply	
• 24 V	Yes; L+ (-0.8 V)
• Output current, max.	900 mA
Power losses	
Power loss, typ.	3 W
Digital inputs	
Input voltage	
• for signal "0"	-3 to +5V
• for signal "1"	11 to 30.2 V
Input current	
• for signal "0", max. (permissible quiescent current)	2 mA
• for signal "1", typ.	9 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", min.	300 µs

<b>Cable length</b>	
• shielded, max.	600 m
<b>Encoder</b>	
Number of connectable encoders, max.	3
<b>Connectable encoders</b>	
• Absolute encoder (SSI)	Yes
• 2-wire sensor	Yes
<b>Encoder signals, absolute encoder (SSI)</b>	
• Cable length, shielded, max.	320 m; 320 m at 125 kHz; 160 m at 250 kHz; 60 m at 500 kHz; 20 m at 1 MHz
<b>Interrupts/diagnostics/status information</b>	
<b>Alarms</b>	
• Diagnostic alarm	Yes
<b>Galvanic isolation</b>	
Galvanic isolation	No
<b>Connection method</b>	
required front connector	20-pin
<b>Dimensions</b>	
Width	40 mm
Height	125 mm
Depth	120 mm
<b>Weights</b>	
Weight, approx.	235 g
<b>last modified:</b>	12.03.2015