

<b>Productname :</b> TUF CUT	<b>Creationdate :</b> 02.11.18 Version : 2.1
<b>Ref.Nr.:</b> UDS000111_3_20181102 (EN)	<b>Replaces:</b> UDS000111_20170629

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	Air purifying respirator equipped with organic gas/vapor cartridge (type A)
<b>hands and skin :</b>	When handling the product wear chemical-resistant gloves (standard EN 374). Use a reusable glove with a minimum breakthrough time of 30 minutes. The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through.
Recommended gloves:	Nitrile
<b>eyes :</b>	Wear safety eyewear according to EN 166.
<b>Environmental protection:</b>	Avoid release to the environment. Collect spillage.
<b>Consumer exposure protection:</b>	Do not eat, drink or smoke when using this product. Use only outdoors or in a well-ventilated area. IF exposed or if you feel unwell: Call a POISON CENTER or doctor/physician.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Propane/butane propelled liquid.
<b>colour :</b>	Brown.
<b>odour :</b>	Oil.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	Not available.
<b>Flash point :</b>	> 100 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	Not available.
<b>lower limit :</b>	Not available.
<b>Vapour pressure :</b>	Not available.
<b>Relative density :</b>	0.970 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Insoluble in water
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	Not available.

### 9.2. Other information

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose



5 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com