

Lever gauge probe

Interapid 312 series



Application:

For measuring deviations in concentricity, axial run-out, parallelism and flatness. For centring shafts of boreholes and aligning workpieces.

Execution:

- Housing with hardened, bolted-on dovetail fixtures
- High sensitivity, low measuring force
- Automatic switching of callipers direction
- Measuring mechanism on ruby bearings

Advantage:

- Art. no. 33300: Angled dial face, simplified reading
- Mounted using dovetail or shaft \varnothing 4 mm

Delivery:

With measuring probe made from hardened steel ball diameter 2 mm, in a case.



Art. no.	33301 020
Brand	TESA
Manufacturer Part Number	074111376
Length measuring range	1.6 mm
Scale value	0.01 mm
Measurement force	0.12 N
Length of measuring sensor from centre of ball	16.5 mm
Material of measuring ball	Steel
Ball diameter	2 mm
Pivot range of measuring sensor	210 Degree
Diameter	30 mm
Connection thread	M1.7
Calibration Group	L
Gross Weight	0.128 kg
Product Group	362

EAN

7630041119183