



# **√**конз 😵 ЮССС

#### Features

- Heavy Industrial CE Approval
- 10 V/m EMI Protection
- Down to ±0.1% Pressure Accuracy
- Down to ±0.75% Total Error Band
- ±3°C Temperature Output Accuracy
- -10°C to +60°C Compensating Temperature
- -20°C to +85°C Operating Temperature

#### **Applications**

- Industrial Process Control and Monitoring
- Advanced HVAC Systems
- Refrigeration Systems
- Automotive Test Stands
- Off-Road Vehicles
- Pumps and Compressors
- Hydraulic/Pneumatic Systems
- Agriculture Equipment
- Energy Generation and Management
- Pool/Spa Pump Monitoring

# **MEAS U5600**

# Wireless Pressure Transducer

- Enhanced Pressure Accuracy
- Digital 24-bit ADC Output, I<sup>2</sup>C Protocol
- Bluetooth<sup>®</sup> 4.0 Wireless Connection
- CE Compliant with a Variety of Pressure Ports
- Compact and Battery Powered [CR2050]
- Optional Stainless Steel Snubber
- Weatherproof (IP66/IP67)
- FCC Certified
- Stainless Steel and Polycarbonate Enclosure
- Gage, Sealed, Absolute, Compound
- iOS, Android<sup>™</sup> and Windows<sup>®</sup> XP/7+ Compatible

The modular U5600 wireless pressure transducer from our UltraStable line is enclosed in a stainless steel and polycarbonate housing. This high accuracy, 24-bit ADC digital output wireless transducer eliminates hard wiring and provides remote process control and monitoring via Bluetooth<sup>®</sup> 4.0 Wireless Communication. This series is suitable for measurement of liquid or gas pressure, even for difficult media such as contaminated water, steam, and mildly corrosive fluids.

The wetted material of the pressure port is made of 316L stainless steel and the transducer's durability is excellent with no o-rings or organics exposed to the pressure media. The U5600 is weatherproof and exceeds the latest heavy industrial CE requirements.

This product is geared to the OEM customer for mid to high volumes. TE stands ready to provide a custom design of the U5600 where the volume and application warrants. Additional configurations not listed are available. Please inquire for further information.

## Standard Ranges

| Range (psi) | Range (Bar) | Gage | Sealed | Absolute | Compound |
|-------------|-------------|------|--------|----------|----------|
| 0 to 005    | 0 to .35    | •    | ٠      | ٠        | •        |
| 0 to 015    | 0 to 001    | •    | •      | ٠        | •        |
| 0 to 030    | 0 to 002    | •    | ٠      | ٠        | •        |
| 0 to 050    | 0 to 3.5    | •    | •      | ٠        | •        |
| 0 to 100    | 0 to 007    | •    | ٠      | ٠        | •        |
|             | 0 to 010    | •    | •      | ٠        | •        |
| 0 to 200    | 0 to 014    | •    | ٠      | ٠        | •        |
| 0 to 300    | 0 to 020    | •    | •      | ٠        | •        |
| 0 to 500    | 0 to 035    | •    | ٠      | ٠        | •        |
| 0 to 01k    | 0 to 070    | •    | ۰      | •        | •        |
| 0 to 03k    | 0 to 200    | •    | •      | •        | ٠        |
| 0 to 05k    | 0 to 350    | •    | •      | •        | ٠        |
| 0 to 10k    | 0 to 700    | •    | •      | •        | •        |

Intermediate ranges available upon request.

## **Performance Specifications**

Ambient Temperature: 25°C (unless otherwise specified) For custom configurations, consult factory.

| Parameters   | Min                    | Тур   | Max             | Units              | Notes                      |  |  |  |
|--|------------------------|---|-----------------|--------------------|----------------------------|--|--|--|
| Supply Voltage   | 2.3                    | 3   | 3.6             | Vdc                | Replaceable CR2050 battery |  |  |  |
| A  | -0.25                  |   | 0.25            | %F.S.              | 5psi                       |  |  |  |
| Accuracy<br>(RSS of linearity, hysteresis, and                     | -0.1                   |   | 0.1             | %F.S.              | >5 and ≤500psi             |  |  |  |
| repeatability)   | -0.25                  |   | 0.25            | %F.S.              | >500 and ≤5000psi          |  |  |  |
|  | -0.75                  |   | 0.75            | %F.S.              | >5000psi                   |  |  |  |
| Temperature Output Accuracy  | -3                     |   | 3               | °C                 |                            |  |  |  |
| Output Protocol  |                        | Digital I <sup>2</sup> C  |                 |                    |                            |  |  |  |
| Resolution   |                        | 24  |                 | Bit                |                            |  |  |  |
| Endurance  | 1.00E+6                |   |                 | 0~FS Cycles        |                            |  |  |  |
| Stability  | -0.25                  |   | 0.25            | %F.S./year         |                            |  |  |  |
| Total Error Band   | -1                     |   | 1               | %F.S.              | 5psi                       |  |  |  |
| (@25°C over compensated range)                                     | -0.75                  |   | 0.75            | %F.S.              | >5 and ≤5000psi            |  |  |  |
|  | -1.25                  |   | 1.25            | %F.S.              | >5000psi                   |  |  |  |
| Proof Pressure   | 3X                     |   | 20k psi         | Rated              |                            |  |  |  |
| Burst Pressure   | 4X                     |   | 20k psi         | Rated              |                            |  |  |  |
| Long Term Stability (1 year)                                       | -0.1                   | -0.1  |                 | %F.S.              |                            |  |  |  |
| Compensated Temperature  | -10                    |   | +60             | °C                 |                            |  |  |  |
| Operating Temperature  | -20                    |   | +85             | °C                 | with battery               |  |  |  |
| Storage Temperature  | -40                    |   | +120            | °C                 | without battery            |  |  |  |
| Wireless Protocol  | Bluetooth®             | Bluetooth® 4.0 Wireless Connection or above   |                 |                    |                            |  |  |  |
| Receiver Operating System  | Android <sup>™</sup> 4 | 1.3 or above  | e, iOS 7 or abo | ove, Windows® XP/7 | 7 or above                 |  |  |  |
| Signal Pairing Distance  | 65 feet                |   |                 |                    |                            |  |  |  |
| Signal Transmission Distance                                       | 65 feet affe           | 65 feet affected by receiver antenna and blocking objects                               |                 |                    |                            |  |  |  |
| Battery Life   | 2 years typi           | 2 years typical CR2050 350mAH battery, 5 second transmission interval, room temperature |                 |                    |                            |  |  |  |
| Low Battery Warning  | 2.5Vdc, red            | 2.5Vdc, red battery symbol in app   |                 |                    |                            |  |  |  |
| Weatherproof   | IP66 & IP67            | 7   |                 |                    |                            |  |  |  |
| Pressure Port Material   | 316L Stainl            | 316L Stainless Steel Port, 316L Stainless Steel Snubber                                 |                 |                    |                            |  |  |  |
| Enclosure  | Stainless S            | Stainless Steel and Polycarbonate   |                 |                    |                            |  |  |  |
| Shock  | 50g, 11mse             | 50g, 11msec Half Sine Shock per MIL-STD-202G, Method 213B, Condition A                  |                 |                    |                            |  |  |  |
| Vibration±20g, MIL-STD-810C, Procedure 514.2, Fig 514.2-2, Curve L |                        |   |                 |                    |                            |  |  |  |

#### Note:

CR2050 Battery not supplied by manufacturer.

Battery life depends on its capacity, operating temperature and signal transmission interval.

Some battery models offer high operating temperatures up to 125°C with nominal capacity 350mAH.

Temperature can impact battery capacity retention even if idle. Check battery specifications for more details.

#### Compliances

EN 55022 Emissions Class A & B

IEC 61000-4-2 Electrostatic Discharge Immunity (4kV contact/8kV air)


IEC 61000-4-3 Radiated, Radio-Frequency Electromagnetic Field Immunity (10V/m, 80M-1GHz); deviation <1.5%

RoHS

FCC

Bluetooth®

# Dimensions [mm]



| Code | Port  | Dim B         | Dim C Ref.   |
|------|---|---------------|--------------|
| 2    | 1/4-19 BSPP   | 0.472 [11.94] | 0.366 [9.3]  |
| 3    | G3/8 JIS B2351  | 0.540 [13.72] | 0.366 [9.3]  |
| 4    | 7/16-20UNF MALE SAE J1926-2 STRAIGHT THREAD<br>O-RING BUNA-N 90SH-904       | 0.433 [11.0]  | 0.366 [9.3]  |
| 5    | 1/4-18 NPT  | 0.600 [15.24] | 0.366 [9.3]  |
| 6    | 1/8-27 NPT  | 0.390 [9.91]  | 0.366 [9.3]  |
| В    | G1/4 JIS B2351  | 0.472 [11.94] | 0.366 [9.3]  |
| E    | 1/4-19 BSPT   | 0.500 [12.7]  | 0.366 [9.3]  |
| F    | 1/4-19 BSPP FEMALE<br>(without snubber)                                     | 0.771 [19.58] | 0.366 [9.3]  |
| Р    | 7/16-20UNF FEMALE SAE J513 STRAIGHT THREAD<br>WITH INTEGRAL VALVE DEPRESSOR | 0.687 [17.5]  | 0.366 [9.3]  |
| Q    | M10 x 1.0 mm ISO 6149-2   | 0.374 [9.5]   | 0.366 [9.3]  |
| Ν    | 7/16-20UNF FEMALE SAE J513 STRAIGHT<br>THREAD                               | 0.687 [17.5]  | 0.366 [9.3]  |
| S    | M12 x 1.5 mm ISO 6149-2   | 0.433 [11.0]  | 0.366 [9.3]  |
| U    | G/14 DIN 3852 FORM E GASKET DIN3869-14 NBR                                  | 0.472 [11.94] | 0.445 [11.3] |
| W    | M20 x 1.5 mm ISO 6149-2   | 0.551 [14.0]  | 0.366 [9.3]  |
| G    | M14 x 1.5 mm ISO 6149-2   | 0.433 [11.0]  | 0.366 [9.3]  |

#### How to Operate

Please refer to the M5600/U5600 Installation Manual and M5600/U5600 Software Manual.

Note: Communication is max 65 feet

#### **Ordering Information**

| U56   | 00 | - | 0 | 0                                    | 00 | 0   | 5   | - | 100P  |  | G  |
|-------|----|---|---|--------------------------------------|----|---|---|---|---|--|--|
| Model | 00 | - | 0 | Snubber                              | 00 | Label   | Pressure Port   | - | - Pressure Range  |  | Pressure Type  |
| U56   | 00 | - | 0 | 0 = No Selection<br>1 = With Snubber | 00 | 0 = Adhesive<br>Label<br>1 = Laser<br>Marking | 2 = 1/4-19 BSPP<br>3 = G3/8 JIS B2351<br>4 = 7/16-20UNF Male SAE<br>J1926-2 Straight Thread O-<br>Ring BUNA-N 90SH-904<br>5 = 1/4-18 NPT<br>6 = 1/8-27NPT<br>B = G1/4 JIS B2351<br>E = 1/4-19 BSPT<br>F = 1/4-19 BSPT<br>F = 1/4-19 BSPP Female<br>P = 7/16-20UNF Female SAE<br>J513 Straight Thread with<br>Integral Valve Depressor<br>Q = M10 x 1.0 mm ISO 6149-2<br>N = 7/16-20UNF FEMALE SAE<br>J513 Straight Thread<br>S = M12 x 1.5 mm ISO 6149-2<br>U = G1/4 DIN 3852 Form E<br>Gasket DIN3869-14 NBR<br>W = M20 x 1.5 mm ISO 6149-2<br>G = M14 x 1.5 mm ISO 6149-2 | - | 015P 00<br>030P 00<br>050P 3.<br>100P 00<br>200P 01<br>300P 02<br>500P 03<br>01KP 07<br>03KP 20<br>05KP 35<br>07KP 50 | 35B<br>01B<br>02B<br>.5B<br>07B<br>10B<br>14B<br>20B<br>35B<br>70B<br>00B<br>50B<br>00B<br>00B | G = Gage<br>S = Sealed<br>A = Absolute<br>C = Compound |

Note: Compound pressure range is -14.7 to xxxpsig or -1 to xxxbarg. (e.g. 200PC: -14.7 to 200psig, 020BC: -1 to 20barg)

#### **NORTH AMERICA**

Measurement Specialties, Inc., a TE Connectivity company 45738 Northport Loop West Fremont, CA 94538 Tel: +1 800 767 1888 Fax: +1 510 498 1578 customercare.frmt@te.com

#### **EUROPE**

MEAS France SAS, a TE Connectivity company 26 Rue des Dames 78340 Les Clayes-sous-Bois, France Tel: +33 (0) 130 79 33 00 Fax: +33 (0) 134 81 03 59 customercare.lcsb@te.com

#### ASIA

Measurement Specialties (China) Ltd., a TE Connectivity company No. 26 Langshan Road Shenzhen High-Tech Park (North) Nanshan District, Shenzhen, 518057 China Tel: +86 755 3330 5088 Fax: +86 755 3330 5099 customercare.shzn@te.com

#### te.com/sensorsolutions

Android is a trademark of Google Inc.

Google Play is a trademark of Google Inc.

iOS is a trademark or registered trademark of Cisco in the U.S. and other countries and is used under license.

Microsoft, Encarta, MSN, and Windows are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries.

Android and Windows are trademarks of their respective owners.

The Bluetooth<sup>®</sup> word mark and logos are registered trademarks owned by the Bluetooth SIG, Inc. and any use of such marks by TE Connectivity is under license. Other trademarks and trade names are those of their respective owners.

Measurement Specialties Inc., a TE Connectivity company.

UltraStable, Measurement Specialties (MEAS), American Sensor Technologies (AST), TE Connectivity, TE Connectivity (logo) and EVERY CONNECTION COUNTS are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2016 TE Connectivity Ltd. family of companies All Rights Reserved.

