
Ultra Subminiature Basic Switch (Sealed) - D2HW

Smallest sealed snap-action switch in the industry with a very long stroke for reliable ON/OFF action

- ROHS Compliant.
- The case dimensions are 78% of conventional models, contributing to down-sizing of mechanical modules.
- Extra-long stroke even without levers, (OT: 1.4mm)



Ordering Information

Model Number Legend:

D2HW-

12345

1. Mounting Structure

- A: Without posts (base-mounting)
- BR: Posts on right
- BL: Posts on left
- C: M3-screw mounting

2. Ratings

2: 1 mA at 5 VDC to 2 A at 12 VDC

3. Actuator

- 0: Pin plunger
- 1: Hinge lever
- 2: Long hinge lever
- 3: Simulated roller hinge lever
- 4: Hinge roller lever
- 6: Leaf lever
- 7: Simulated roller leaf lever
- 8: Long leaf lever

4. Contacts

- 1: SPDT
- 2: SPST-NC (Molded lead wire models only.)
- 3: SPST-NO (Molded lead wire models only.)

5. Terminals

- D: Straight PCB terminals
- DR: Right-angled PCB terminals
- DL: Left-angled PCB terminals
- H: Solder terminals
- M: Molded lead wires downwards
- MR: Molded lead wires on right-side
- ML: Molded lead wires on left-side
- Note Add "S" to the end of the model number for the UL/CSAapproved version.

List of Models

PCB-mounted Models

Actuator	Terminals		Contact form	Model		
				With posts on right	With posts on left	Without posts
Pin plunger	For PCB	Straight Angled	SPDT	 D2HW-BR201DR	 D2HW-BL201DL	D2HW-A201D
Hinge lever	-	Straight Angled	-	 D2HW-BR211DR	 D2HW-BL211DL	D2HW-A211D
	-	Straight	-			D2HW-A221D
Long hinge lever		Angled	•	D2HW-BR221DR	D2HW-BL221DL	
Simulated roller hinge lever		Straight Angled		 D2HW-BR231DR	 D2HW-BL231DL	D2HW-A231D

Note Add "S" to the end of the model number for the UL/CSA-approved version. Consult your OMRON representative for details.

Models with Solder Terminals or Molded Lead Wires

Actuator	Te	rminals	Contact form		Model	
				With posts on right	With posts on left	M3-screw mounting
Dia alta anti	Solder		SPDT	D2HW-BR201H	D2HW-BL201H	D2HW-C201H
Pin plunger	Molded lead	Downwards	SPDT	D2HW-BR201M	D2HW-BL201M	D2HW-C201M
	wires		SPST-NC	D2HW-BR202M	D2HW-BL202M	D2HW-C202M
			SPST-NO	D2HW-BR203M	D2HW-BL203M	D2HW-C203M
		Right-side	SPST-NC	D2HW-BR202MR	D2HW-BL202MR	D2HW-C202MR
			SPST-NO	D2HW-BR203MR	D2HW-BL203MR	D2HW-C203MR
		Left-side	SPST-NC	D2HW-BR202ML	D2HW-BL202ML	
			SPST-NO	D2HW-BR203ML	D2HW-BL203ML	
	Solder	Solder		D2HW-BR211H	D2HW-BL211H	D2HW-C211H
Hinge lever	Molded lead	Downwards	SPDT	D2HW-BR211M	D2HW-BL211M	D2HW-C211M
	wires	wires	SPST-NC	D2HW-BR212M	D2HW-BL212M	D2HW-C212M
			SPST-NO	D2HW-BR213M	D2HW-BL213M	D2HW-C213M
		Right-side	SPST-NC	D2HW-BR212MR	D2HW-BL212MR	D2HW-C212MR
			SPST-NO	D2HW-BR213MR	D2HW-BL213MR	D2HW-C213MR
		Left-side	SPST-NC	D2HW-BR212ML	D2HW-BL212ML	
			SPST-NO	D2HW-BR213ML	D2HW-BL213ML	
Long hinge	Solder		SPDT	D2HW-BR221H	D2HW-BL221H	D2HW-C221H
lever	Molded lead	Downwards	SPDT	D2HW-BR221M	D2HW-BL221M	D2HW-C221M
/	wires	wires	SPST-NC	D2HW-BR222M	D2HW-BL222M	D2HW-C222M
<u> </u>			SPST-NO	D2HW-BR223M	D2HW-BL223M	D2HW-C223M
		Right-side	SPST-NC	D2HW-BR222MR	D2HW-BL222MR	D2HW-C222MR
			SPST-NO	D2HW-BR223MR	D2HW-BL223MR	D2HW-C223MR
		Left-side	SPST-NC	D2HW-BR222ML	D2HW-BL222ML	
			SPST-NO	D2HW-BR223ML	D2HW-BL223ML	

Note: 1. The length of standard lead wires (AVSS0.5) for molded lead wire models is 30 cm.

2. Add "S" to the end of the model number for the UL/CSA-approved version. Consult your OMRON representative for details.

Ultra Subminiature Basic Switch (Sealed) – D2HW

Actuator	Te	rminals	Contact form		Model	
				With posts on right	With posts on left	M3-screw mounting
	Solder		SPDT	D2HW-BR231H	D2HW-BL231H	D2HW-C231H
Simulated roller hinge lever	Molded lead	Downwards	SPDT	D2HW-BR231M	D2HW-BL231M	D2HW-C231M
	wires	Downwards	SPST-NC	D2HW-BR232M	D2HW-BL232M	D2HW-C232M
~			SPST-NO	D2HW-BR233M	D2HW-BL233M	D2HW-C233M
		Right-side	SPST-NC	D2HW-BR232MR	D2HW-BL232MR	D2HW-C232MR
		Tugine side	SPST-NO	D2HW-BR233MR	D2HW-BL233MR	D2HW-C233MR
		Left-side	SPST-NC	D2HW-BR232ML	D2HW-BL232ML	
		Leit-side	SPST-NO	D2HW-BR233ML	D2HW-BL232ML	
	Solder		SPDT	D2HW-BR241H	D2HW-BL241H	D2HW-C241H
Hinge roller lever	Molded lead	Downwards	SPDT	D2HW-BR241M	D2HW-BL241M	D2HW-C241M
level 9	wires	Downwarus	SPST-NC	D2HW-BR241M	D2HW-BL241M D2HW-BL242M	D2HW-C241M
<u> </u>			SPST-NO	D2HW-BR243M	D2HW-BL242M	D2HW-C242M
		Right-side	SPST-NC	D2HW-BR243M D2HW-BR242MR	D2HW-BL243M D2HW-BL242MR	D2HW-C243M
		Right-side	SPST-NO	D2HW-BR242MR	D2HW-BL243MR	D2HW-C243MR
		Left-side	SPST-NO SPST-NC	D2HW-BR243MR	D2HW-BL243MR	D2HW-0243MR
		Lett-side	SPST-NC SPST-NO	D2HW-BR242ML D2HW-BR243ML	D2HW-BL242ML D2HW-BL243ML	
	Solder		SPDT	D2HW-BR243ML D2HW-BR261H		 D2HW-C261H
Leaf lever	Molded lead	Downwards	SPDT	D2HW-BR261H	D2HW-BL261H D2HW-BL261M	D2HW-C261M
	wires	Downwards	SPDT SPST-NC	D2HW-BR261M D2HW-BR262M	D2HW-BL261M	D2HW-C261M
			SPST-NC SPST-NO	D2HW-BR262M	D2HW-BL262M	D2HW-C262M
		Dista side	SPST-NC	D2HW-BR263M D2HW-BR262MR	D2HW-BL263M D2HW-BL262MR	D2HW-C263M
		Right-side	SPST-NC SPST-NO			
		1.0.11	SPST-NC	D2HW-BR263MR D2HW-BR262MI	D2HW-BL263MR	D2HW-C263MR
		Left-side			D2HW-BL262ML	
			SPST-NO	D2HW-BR263ML	D2HW-BL263ML	
Simulated roller	Solder		SPDT	D2HW-BR271H	D2HW-BL271H	D2HW-C271H
leaf lever	Molded lead wires	Downwards	SPDT	D2HW-BR271M	D2HW-BL271M	D2HW-C271M
<u> </u>			SPST-NC	D2HW-BR272M	D2HW-BL272M	D2HW-C272M
			SPST-NO	D2HW-BR273M	D2HW-BL273M	D2HW-C273M
		Right-side	SPST-NC	D2HW-BR272MR	D2HW-BL272MR	D2HW-C272MR
		L	SPST-NO	D2HW-BR273MR	D2HW-BL273MR	D2HW-C273MR
		Left-side	SPST-NC	D2HW-BR272ML	D2HW-BL272ML	
		-	SPST-NO	D2HW-BR273ML	D2HW-BL273ML	
Long leaf lever	Molded lead wires	Downwards	SPDT	D2HW-BR281M	D2HW-BL281M	D2HW-C281M
Γ Γ	1 1103		SPST-NC	D2HW-BR282M	D2HW-BL282M	D2HW-C282M
_			SPST-NO	D2HW-BR283M	D2HW-BL283M	D2HW-C283M
		Right-side	SPST-NC			D2HW-C282MR
			SPST-NO			D2HW-C283MR

Note: 1. The length of standard lead wires (AVSS 0.5) for molded lead wire models is 30 cm.

2. Add "S" to the end of the model number for the UL/CSA-approved version. Consult your OMRON representative for details.

Specifications -

Ratings

Rated voltage (V)	Resistive load
125 VAC	0.1 A
12 VDC	2 A
24 VDC	1 A
42 VDC	0.5 A

Note: The ratings values apply under the following test conditions:

Ambient temperature:20±2Ambient humidity:65±5Operating frequency:30 op

20±2°C 65±5% 30 operations / min

Characteristics

ltem	Specification
Operating speed	1 mm to 500 mm/s (for pin plunger models)
Operating frequency	30 operations/min
Insulation resistance	100 MΩ min. (at 500 VDC)
Contact resistance (initial value)	100 m Ω max. (molded lead wire models: 150 m Ω max.)
Dielectric strength	600 VAC, 50/60 Hz for 1 min between terminals of the same polarity 1,500 VAC, 50/60 Hz for 1 min between current-carrying metal parts and ground, and between each terminal and non-current-carrying metal parts
Vibration resistance (see note 2)	Malfunction: 10 to 55 Hz, 1.5-mm double amplitude
Shock resistance (see note 2)	Destruction: 1,000 m/s ² {approx. 100 G} max. Malfunction: 300 m/s ² {approx. 30 G} max.
Durability (see note 3)	Mechanical: 1,000,000 operations min. (30 operations/min) Electrical: 100,000 operations min. (20 operations/min)
Degree of protection IEC IP67 (excluding the terminals on terminal models)	
Degree of protection against electric shock	Class I
Proof tracking index (PTI) 175	
Ambient operating temperature	-40 to 85°C (with no icing)
Ambient operating humidity	95% max. (for 5 to 35°C)
Weight	Approx. 0.7 g (for pin plunger models with terminals)

Note: 1. The data given above are initial values.

2. For the pin plunger models, the above values apply for use at the free position, operating position, and total travel position. For the lever models, they apply at the total travel position.

The values shown apply for malfunctions of 1 ms max.

3. For testing conditions, contact your OMRON sales representative.

Approved Standards

UL1054 (File No. E41515)/CSA C22.2 No. 55 (cUL approval)

Consult your OMRON sales representative for models with standard approval.

Rated voltage	D2HW
125 VAC	0.1 A
12 VDC	2 A

Contact Specifications

ltem	Specification
Specification	Crossbar
Material	Gold alloy
Gap (standard value)	0.5 mm
Minimum applicable load (see note)	1 mA at 5 VDC

Note Minimum applicable loads are indicated by N standard reference values. This value represents the failure rate at a 60% (λ60) reliability level.

The equation λ 60=035×10–6/operations indicates that a failure rate of 1/2,000,000 operations can be expected at a reliability level of 60%.

Contact Form

SPDT

SPST-NC (Molded Lead Wire Models Only)







Note Molded lead wire colors are indicated in parentheses.

SPST-NO (Molded Lead Wire Models Only)




Dimensions -


Mounting Structure and Reference Positions for Operating Characteristics

Note All units are in millimeters unless otherwise indicated.

The reference positions used for FP, OP, and TTP values are as shown below for each type of mounting.



Mounting Hole Dimensions (Reference) Mounting Hole Dimensions (Reference)



Ô

2.4^{+0.1} dia. hole (depth: 5 mm mir

6+0


Ó

-(13.3)

(12)




Terminals



PCB Cutout Dimensions (Reference)



Molded Lead Wires on Left-side



Note: UL1007 AWG24 wires are used for UL/CSA approved models.

Ó Three-0.6 0.5 5 08+ 13 1

PCB Cutout Dimensions (Reference)

5.08±015.08±0

Ó

2.6

AVSS 0.5


(5)

-300±14

Angled PCB Terminals

Solder Terminals 3.5 1.8 0.5 Three-2 4 38 4 35

Molded Lead Wires Downwards



Note: Angled terminal directions are shown below.



TD

Right-angled terminal

Left-angled terminal

Dimensions and Operating Characteristics

Note: 1. All units are in millimeters unless otherwise indicated.


- 2. Dimensions not indicated in the above diagrams have a tolerance of ± 0.2 mm.
- 3. The operating characteristics are for operation in the A direction ($_{\underline{A}}$).

Charac- teristic	Models without posts	Models with posts and M3-mounting models
OF max.	0.75 N {76 gf}	
RF min.	0.10 N {10 gf}	
OT ref.	(1.4 mm)	
MD max.	0.25 mm	
FP max.	11.2 mm	7.2 mm
OP	10.4±0.2 mm	6.4±0.2 mm
TTP max.	9.1 mm	5.1 mm

Hinge Lever Models

D2HW-_21__






Charac- teristic	Models without posts	Models with posts and M3-mounting models	
OF max.	0.75 N {76 gf}		
RF min.	0.07 N {7 gf}		
OT ref.	(1.6 mm)		
MD max.	0.5 mm		
FP max.	12.8 mm	8.8 mm	
OP	11.5±0.5 mm	7.5±0.5 mm	
TTP max.	10 mm	6 mm	

Long Hinge Lever Models






Charac-Models without Models with posts teristic posts and M3-mounting models OF max. 0.5 N {50 gf} 0.03 N {3 gf} RF min. OT ref. (2.5 mm) MD max. 0.8 mm FP max. 15.5 mm 11.5 mm OP 13.3±0.8 mm 9.3±0.8 mm TTP max. 11 mm 7 mm

Simulated Roller Hinge Lever Models D2HW-L23






Charac- teristic	Models without posts	Models with posts and M3-mounting models	
OF max. RF min.	0.65 N {66 gf} 0.05 N {5 qf}		
	1.01		
OT ref. MD max.	(1.9 mm) 0.5 mm		
FP max.	16.5 mm	12.5 mm	
OP	15.2±0.5 mm	11.2±0.5 mm	
TTP max.	13.5 mm	9.5 mm	

Ultra Subminiature Basic Switch (Sealed) – D2HW

Hinge Roller Lever Models

D2HW-__24____






Characteristic	Models with posts and M3-mounting models
OF max.	0.65 N {66 gf}
RF min.	0.03 N {3 gf}
OT ref. MD max.	(1.9 mm) 0.6 mm
FP max.	15.3 mm
OP	14±0.6 mm
TTP max.	12.3 mm

Leaf Lever Models

D2HW-__26___






Characteristic	Models with posts and M3-mounting models
OF max.	1.8 N {183 gf}
RF min.	0.20 N {20 gf}
OT ref.	(1.8 mm)
MD max.	0.5 mm
FP max.	9.3 mm
OP	7.4±0.5 mm
TTP max.	5.8 mm

Simulated Roller Leaf Lever Models

D2HW-__27___






Characteristic	Models with posts and M3-mounting models
OF max.	1.8 N {183 gf}
RF min.	0.20 N {20 gf}
OT ref.	(2.0 mm)
MD max.	0.5 mm
FP max.	12.5 mm
OP	10.8±0.5 mm
TTP max.	8.9 mm

Characteristic	Models with posts and M3-mounting models
OF max.	0.9 N {92 gf}
RF min.	0.05 N {5 gf}
OT ref.	(2.8 mm)
MD max.	0.7 mm
FP max.	19 mm
OP	15.4±1.5 mm
TTP max.	12.8 mm

Long Leaf Lever Models D2HW-□28□□



Note: UL1007 AWG24 wires are used for UL/CSA approved models.

Precautions

Cautions

Degree of Protection

Do not use this product in water. Although molded lead wire models satisfy the test conditions for the standard given below, this test is to check the ingress of water into the switch enclosure after submerging the Switch in water for a given time. Satisfying this test condition does not mean that the Switch can be used in water.

IEC Publication 529, degree of protection IP67.

Do not operate the Switch when it is exposed to water spray, or when water drops adhere to the Switch surface, or during sudden temperature changes, otherwise water may intrude into the interior of the Switch due to a suction effect.

Prevent the Switch from coming into contact with oil and chemicals. Otherwise, damage to or deterioration of Switch materials may result.

Do not use the Switch in areas where it is exposed to silicon adhesives, oil, or grease, otherwise faulty contact may result due to the generation of silicon oxide.

Terminal Connection

When soldering the lead wire to the terminal, first insert the lead wire conductor through the terminal hole and then conduct soldering.

Made sure that the capacity of the soldering iron is 30 W maximum. Do not take more than 3 s to solder the switch terminal. Improper soldering involving an excessively high temperature or excessive soldering time may deteriorate the characteristics of the Switch.

When soldering the lead wire to the PCB terminal, pay careful attention so that the flux and solder liquid level does not exceed the PCB level.

Side-actuated (Cam/Dog) Operation

When using a cam or dog to operate the Switch, factors such as the operating speed, operating frequency, push-button indentation, and material and shape of the cam or dog will affect the durability of the Switch. Confirm performance specifications under actual operation conditions before using the Switch in applications.

Correct Use

Mounting

Turn OFF the power supply before mounting or removing the Switch, wiring, or performing maintenance or inspection. Failure to do so may result in electric shock or burning.

For M3-screw mounting models, use M3 mounting screws with plane washers or spring washers to securely mount the Switch. Tighten the screws to a torque of 0.29 N·m {3 kgf·cm}. Exceeding the specified torque may result in deterioration of the sealing or damage.

For models with posts, secure the posts by thermal caulking or by pressing into an attached device. When pressed into an attached device, provide guides on the opposite ends of the posts to ensure that they do not fall out or rattle.

Mount the Switch onto a flat surface. Mounting on an uneven surface may cause deformation of the Switch, resulting in faulty operation or damage.


Operating Body

Use an operating body with low frictional resistance and of a shape that will not interfere with the sealing rubber, otherwise the plunger may be damaged or the sealing may deteriorate.

Handling

Do not handle the Switch in a way that may cause damage to the sealing rubber.

When handling the Switch, ensure that pressure is not applied to the posts in the directions shown in the following diagram. Also, ensure that uneven pressure or pressure in a direction other than the operating direction is not applied to the Actuator as shown in the following diagram. Otherwise, the post, Actuator, or Switch may be damaged, or the service life may be reduced.



Wiring Molded Lead Wire Models

When wiring molded lead wire models, ensure that there is no weight on the wire or that there are no sharp bends near the parts where the wire is drawn out. Otherwise, damage to the Switch or deterioration in the sealing may result.

Using Micro Loads

Even when using micro load models within the operating range, inrush currents or surges may decrease the life expectancy of the Switch. Therefore, insert a contact protection circuit where necessary.

ALL DIMENSIONS SHOWN ARE IN MILLIMETRES.

To convert millimetres into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

