XCKJ10541

limit switch XCKJ - th.plastic roller lever var. length - 1NC+1NO - snap - Pg13





Main

Range of product	OsiSense XC
Series name	Standard format
Product or component	Limit switch
type	
Device short name	XCKJ
Sensor design	-
Body type	Fixed
Head type	Rotary head
Material	Metal
Body material	Zamak
Head material	Zamak
Fixing mode	By the body
Movement of operating head	Rotary
Type of operator	Spring return roller lever thermoplastic variable length
Type of approach	Lateral approach, 1 or 2 programmable direction
Cable entry	1 entry tapped for Pg 13.5 cable gland, cable outer diameter: 912 mm
Number of poles	2
Contacts type and composition	1 NC + 1 NO
Contact operation	Snap action

Complementary

(1.5 mm²
-5-1 appendix A 947-5-1 appendix A
/, operating rate <60 cyc/ dix C /, operating rate <60 cyc/ dix C operating rate <60 cyc/ dix C
dia /, dia dia op

Height	3.03 in (77 mm)	
Depth	1.73 in (44 mm)	
Net Weight	1.07 lb(US) (0.485 kg)	
Terminals description ISO n°1	(21-22)NC (13-14)NO	

Environment

Liviloriment	
Shock resistance	50 gn 11 ms IEC 60068-2-27
Vibration resistance	25 gn 10500 Hz)IEC 60068-2-6
IP degree of protection	IP66 IEC 60529
IK degree of protection	IK07 conforming to EN 50102
Overvoltage category	Class I IEC 61140 Class I NF C 20-030
Ambient air temperature for operation	-13158 °F (-2570 °C)
Ambient air temperature for storage	-40158 °F (-4070 °C)
Protective treatment	TC
Product certifications	CCC UL CSA
Standards	CENELEC EN 50041 EN 60204-1 CSA C22.2 No 14 IEC 60204-1 UL 508 EN 60947-5-1 IEC 60947-5-1

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ	
Discount Schedule	Т	
GTIN	00785901230984	
Nbr. of units in pkg.	1	
Package weight(Lbs)	1.04 lb(US) (0.47 kg)	
Returnability	Yes	
Country of origin	ID	

Packing Units

Package 1 Height	0.430 dm	
Package 1 width	0.700 dm	
Package 1 Length	1.280 dm	


Offer Sustainability Sustainable offer status

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh Regulation	REACh Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EVEN RoHS Declaration
Mercury free	Yes
RoHS exemption information	€Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

	•
Warranty	18 months

Dimensions




(1) 1 tapped entry Pg 13.5

XCKJ10541

Mounting with Cable Entry


Position of Cable Gland



- Recommended (1)
- To be avoided (2)

Mounting with Rotary Heads and Levers


Type of Cam





- Recommended
- To be avoided

Setting-up with Lever Head



- 5° steps throughout 360° / Tightening torque (Min : 1) (Max : 1.5) 45° steps throughout 360° / Tightening torque (Min : 1) (Max : 1.5)
- Tightening torque (Min: 1) (Max: 1.5)

Setting-up with Head ZCKE05

Direction of Actuation Programming



Product data sheet Connections and Schema

XCKJ10541

Wiring Diagram

2-pole NC + NO Snap Action



Product data sheet **Technical Description**


XCKJ10541

Characteristics of Actuation

Switch Actuation by 30° Cam



Functionnal Diagram



- (2) (3)
- (1) Closed
- Open
- (3) Tripping (4) Resetting