

## Miniature cutting insert, type AG HC5640

For internal recessing

**ATORN**<sup>®</sup>



### Application

For internal recessing in the material groups steel and (stainless steel) at low to high cutting speeds and under average cutting conditions.

### Version

- Solid carbide cutting insert with internal cooling

### Advantage

- Tough cemented carbide grade for a broad scope of application
- Stable geometry for the cutting insert
- Ideal for use with low-performance machines and unstable cutting conditions

<b>Art. no.</b>	<b>17129 264</b>
<b>ISO name</b>	AG
<b>Shaft diameter</b>	8 mm
<b>Length</b>	64 mm
<b>Clearance length</b>	22 mm
<b>Programming size 2</b>	1.7 mm
<b>Recessing width</b>	1.5 mm
<b>Programming size</b>	3.8 mm
<b>Min. bore diameter</b>	8.1 mm
<b>Machining direction</b>	Left
<b>Carbide type</b>	HC5640
<b>Material to be processed</b>	Steel, Stainless steel, Non-ferrous metal, Cast metal

### EAN-Code

4050293377484