

Combination wrench (DIN 3113 A) with special coating

DIN 3113 A, jaw angle 15°, ring side angled 15°

ATORN[®]



Version

- With completely new special surface
- Maximum resistance against contact corrosion
- 15x greater corrosion protection against exposure to temperature, road salt and environmental influences compared to conventionally coated keys
- Up to 720 hours in the salt spray test in accordance with DIN EN ISO 9227
- Environmentally friendly chromium-VI-free coating process
- Made from chromium-vanadium steel, die-forged and hardened.
- DIN 3113 A

Advantage

- Extremely durable and robust industrial design

Art. No.	52034 005
Width across flats	5.5 mm
Length	92 mm
Tip profile type	ENERGY profile
Jaw position	15 Degree
Surface	Special coating according to specifications
Material	Chrome-vanadium steel
DIN	3113

EAN-Code

4050293536881