

Product Data Sheet

Updated : October 1994 Supersedes : All Previous

Product Description

9527 is a medium-firm rubber-resin pressure sensitive adhesive system. It features an excellent balance of high initial adhesion and good holding power to a wide variety of materials.

Physical Properties Not for specification purposes

Adhesive Type	Medium Firm Rubber	3M ref :
Carrier	Paper	
Thickness (ASTM D-3652)		
Tape	0.13 mm	
Liner	0.13 mm	
Total	0.26 mm	
Release Liner	Brown Paper	
Shelf Life	12 months from date of despatch by 3M when stored in the	
	original carton at 21°C (70°F) & 50% Relative Humidity	

Performance Characteristics

Not for specification purposes

Adhesion to Stainless Steel ASTM D-3330	6.0 N/10mm	
Temperature Performance Max : Minutes / Hours Max : Days / Weeks	70 °C 50 °C	
Solvent Resistance	Medium	
UV Light Resistance	Not recommended for direct exposure to sunlight or other sources of ultra-violet light.	

Date: October 1994 9527 Double Coated Tape

Application Techniques

- 1. Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure develops better adhesive contact & thus improves bond strength.
- 2. To obtain optimum adhesion, the bonding

surfaces must be clean dry and well unified. A typical surface cleaning solvent is isopropyl alcohol & water. Use proper safety precautions for handling solvents.

3. Ideal tape application temperature range is 21°C to 38°C (70°F to 100°F).

Initial tape application to surfaces at temperatures below 10°C (50°F) is not recommended because the adhesive becomes too firm to adhere readily. However once properly applied low temperature holding is generally satisfactory.

Applications

9527 is well suited for bonding together a wide variety of similar and dissimilar materials such as rubbers, metals, wood, glass, paints and many plastics.

Some typical applications include:

Splicing of papers, foils, films, fabrics etc.

Mounting rubber or photopolymer printing plates

Miscellaneous joining, holding and mounting uses where high adhesion and holding power are required.

3M is a trademark of the 3M Company.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications.

This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.



Specialty Tapes & Adhesives

Customer Service :

Tel 0161 236 8500 Fax 0161 237 1105 3M Ireland 3M House, Adelphi Centre, Upper Georges Street, Dun Laoghaire, Co. Dublin, Ireland © 3M United Kingdom PLC 1996

Tel (01) 280 3555 Fax (01) 280 3509

Customer Service: