Connection Line M12 x 1; 8-pin

S88W-10MPUR

Part Number







Technical Data

Mechanical Data				
Connection 1	Socket, angled			
Connection mode 1	M12 × 1, 8-pin			
Connection 2	stripped			
Torque	M12: 0,5 Nm			
Cable Length	10 m			
Cable Diameter	6,6 mm			
Wire cross-section	0,25 mm ²			
Degree of Protection	IP67			
Temperature Range	-2580 °C			
Cable Jacket Material	PUR			
Material Wire Insulation	PP			
Material Sleeve Nut	CuZn, nickel-plated			
Screened	yes			
Halogen-free	yes			
Drag Chain Suitable	yes			
Bending radius (fixed installation)	> 5 × d			
Bending radius (used in motion)	> 10 × d			
Travel speed (with 5 m horizontal travel distance)	≤ 3,3 m/s			
Acceleration	≤ 5 m/s²			
Bending cycles	> 2000000			
Packaging unit	1 Piece			
Connection Diagram No.	S17			
Connection Equipment No.	88			

- Halogen free, drag chain suitability
- PUR, angled
- Screened







.egen	nd		PT	Platinum measuring resistor	ENAR9422	Encoder A/Ā (TTL)	
+	Supply Voltage +		nc	not connected	ENBRS422	Encoder B/B (TTL)	
-	Supply Voltage 0 V		U	Test Input	ENA	Encoder A	
~	Supply Voltage (AC Voltage)		Ū	Test Input inverted	ENB	Encoder B	
Α	Switching Output	(NO)	W	Trigger Input	Amin	Digital output MIN	
Ā	Switching Output	(NC)	W-	Ground for the Trigger Input	Амах	Digital output MAX	
V	Contamination/Error Output	(NO)	0	Analog Output	Аок	Digital output OK	
V	Contamination/Error Output	(NC)	0-	Ground for the Analog Output	SY In	Synchronization In	
E	Input (analog or digital)		BZ	Block Discharge	SY OUT	Synchronization OUT	
Т	Teach Input		Awv	Valve Output	OLT	Brightness output	
Z	Time Delay (activation)		а	Valve Control Output +	М	Maintenance	
S	Shielding		b	Valve Control Output 0 V	rsv	reserved	
RxD	Interface Receive Path		SY	Synchronization	Wire Co	Wire Colors according to DIN IEC 757	
TxD	Interface Send Path		SY-	Ground for the Synchronization	BK	Black	
RDY	Ready		E+	Receiver-Line	BN	Brown	
GND	Ground		S+	Emitter-Line	RD	Red	
CL	Clock		±	Grounding	OG	Orange	
E/A	Output/Input programmable		SnR	Switching Distance Reduction	YE	Yellow	
0	IO-Link		Rx+/-	Ethernet Receive Path	GN	Green	
PoE	Power over Ethernet		Tx+/-	Ethernet Send Path	BU	Blue	
IN	Safety Input		Bus	Interfaces-Bus A(+)/B(-)	VT	Violet	
OSSD	Safety Output		La	Emitted Light disengageable	GY	Grey	
Signal	Signal Output		Mag	Magnet activation	WH	White	
	Ethernet Gigabit bidirect, data	line (A-D)	RES	Input confirmation	PK	Pink	
	Encoder 0-pulse 0-0 (TTL)	. ,	EDM	Contactor Monitoring	GNYE	Green/Yellow	