

Piloted counterbore, 180°, with removable pilot, carbide-tipped

For universal use up to 1300 N/mm²



Application:

For producing 180° counterbores in connection with interchangeable pilots in steel, stainless steel, non-ferrous metals, cast and special alloy material groups up to a strength of 1300 N/mm² in single part production.

Execution:

- carbide-tipped piloted counterbore with removable pilot and a straight cutting edge, three cutting edges

Advantage:

- Special geometry ensures high machining rates in both short- and long-chipping materials
- long service life due to high-quality cemented carbide and high-strength soldering
- innovative cutting geometry provides excellent cutting performance and good finish quality



Art. no.	11543 220
Brand	HERMANN BILZ
Manufacturer Part Number	A 220305
Construction size	3
Spot-facer diameter	22 mm
Hole diameter of mount	5 mm
Manufactured part diameter	6.6 mm
Thread dimension	M6
Projecting length	34 mm
Length	56 mm
Number of cutting edges	3 PCS
Cutting material	Carbide
Gross Weight	0.080 kg
Product Group	116