



Technical data

General specifications

Fiber optic length	l	1000 mm
Fiber optic diameter	d	7.3 mm
Adapter form		04
End piece		thread
Bending radius		min. 20 mm
Fiber bundle diameter		1.8 mm optical face: 2.5 mm ²
Angle of divergence		approx. 68 °

Ambient conditions

Ambient temperature	-20 ... 85 °C (-4 ... 185 °F) [Adapter] -40 ... 180 °C (-40 ... 356 °F) [End head and Covering]
Storage temperature	-20 ... 85 °C (-4 ... 185 °F)

Mechanical specifications

Protection degree	IP65
Material	
Optical face	glass
Sheathing	Metal-silicon
Core	Glass fiber
End piece	Stainless steel 1.4305 / AISI 303
Adapter	PVC
Extraction force	at probe at 20°C: 120 N

Model Number

LLE 04-1,6-1,0-G

Glass fiber optic - thru-beam with metal silicone covering
M6 threading

Features

- Chemical-resistant
- Thread M6

Series

Fiber optic amplifiers

Device series	MLV41-LL
---------------	----------

Description

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Dimensions

