


	<p>0055JD</p> <p>ERSA 50 S soldering iron, 50 W, 230 V, complete with ERSADUR tip 0052JD and holder 0A04</p>	<p><u>Soldering tips:</u></p> <p>0052JD/SB ERSADUR, chisel-shaped, bent, 3.1 mm/0.122 in</p> <p>0052JD/10 ERSADUR, chisel-shaped, bent, 3.1 mm/0.122 in</p> <p><u>Accessories / spare parts:</u></p> <p>0A04 Holder for ERSA 50 S</p> <p>E005100 Heating element for ERSA 50 S, 230 V, 50 W</p>
	<p>0085JD</p> <p>ERSA 80 S soldering iron, 80 W, 230 V, complete with ERSADUR tip 0082JD and holder 0A04</p>	<p><u>Soldering tips:</u></p> <p>0082JD/SB ERSADUR, chisel-shaped, bent, 4.8 mm/0.189 in</p> <p>0082JD/10 ERSADUR, chisel-shaped, bent, 4.8 mm/0.189 in</p> <p>0082KD/SB ERSADUR, chisel-shaped, 4.8 mm/0.189 in</p> <p><u>Accessories / spare parts:</u></p> <p>0A04 Holder for ERSA 80 S</p> <p>E008100 Heating element for ERSA 80 S, 230 V, 80 W</p>
	<p>0155JD</p> <p>ERSA 150 S soldering iron, 150 W, 230 V, complete with ERSADUR tip 0152JD and holder 0A04</p>	<p><u>Soldering tips:</u></p> <p>0152JD/SB ERSADUR, chisel-shaped, bent, 5.3 mm/0.209 in</p> <p>0152JD/10 ERSADUR, chisel-shaped, bent, 5.3 mm/0.209 in</p> <p>0152KD/SB ERSADUR, chisel-shaped, 5.3 mm/0.209 in</p> <p>0152KD/10 ERSADUR, chisel-shaped, 5.3 mm/0.209 in</p> <p><u>Accessories / spare parts:</u></p> <p>0A04 Holder for ERSA 150 S</p> <p>E015100 Heating element for ERSA 150 S, 230 V, 150 W</p>
	<p>0185PZ</p> <p>ERSA 185 PZ plastics welding device, 150 W, 230 V, complete with welding blade 0182PZ004, holder 0A38 and cleaning brush</p>	<p><u>Welding blade:</u></p> <p>0182PZ004 Welding blade for ERSA 185 PZ</p> <p><u>Accessories / spare parts:</u></p> <p>E015100 Heating element for ERSA 185 PZ, 230 V, 150 W</p> <p>3ZT00051 Cleaning brush, bristles made of brass wire</p>