

166-90305

Article Number: 166-90305



Description: HelaGuard Non-Metallic IP66 Fitting, Straight, 1/2" NPT Thread, 0.38" Dia, PA66, Black, 10/pkg

| | | |
|-------------------------------|-----------------------|---|
| Base Data | Local Order Number | 166-90305 |
| | Type | HG038-S-0500 |
| | Color | Black (BK) |
| | Features and benefits | <ul style="list-style-type: none"> • External NPT thread provides a secure connection. • Snap-on construction reduces installation time and costs by eliminating the need to thread fittings onto conduits. • All-around "teeth" attach firmly to conduit and deliver a high extraction force. • Durable nylon material has high resistance to salts, oils, weak acids and solvents. • IP66 fitting has one-piece construction. • IP68 fitting has additional conduit seal for increased protection against wind, dirt and water. |
| | Quantity Per | bag |
| | Product Description | Straight fitting features a snap-on design that provides a quick, secure connection. Constructed of a very durable nylon material with a high resistance to salts, oils, weak acids and solvents. Designed for easy removal with a small screwdriver. Choose from IP66 or IP68 ingress protection rated fittings. |
| | Short Description | HelaGuard Non-Metallic IP66 Fitting, Straight, 1/2" NPT Thread, 0.38" Dia, PA66, Black, 10/pkg |
| | Product Dimensions | Length L (Imperial) |
| Length L (Metric) | | 44mm |
| Outside Diameter D (imperial) | | 1.14" |
| Outside Diameter D (metric) | | 29mm |
| Nominal Diameter (Imperial) | | 3/8" |
| Nominal Diameter (Metric) | | 16mm |
| Material and Specifications | | Material |
| | Material Shortcut | PA66 |
| | Flammability | UL 94 V2 |
| | | |

166-90305



| | | |
|-----------------------------|-----------------------------|-----------------------------------|
| Material and Specifications | Operating Temperature | -58°F to +275°F (-50°C to +135°C) |
| | | |
| Logistic and Packaging | | |
| | Package Quantity (Imperial) | 10 |
| | Package Quantity (Metric) | 10Pieces |
| | Customs Number(Schedule B) | 3926909987 |