

T8 Luxline Plus FEP

F58w/T8/840 Shatter-Proof Fep
0001494

Product features

- T8 Luxline Plus FEP



PRODUCT OVERVIEW

Product name	F58w/T8/840 Shatter-Proof Fep
Technology	Fluorescent
Watt (Rated) (W)	58.00
Lamp shape	Tube, double-ended
Type	T8 Luxline Plus FEP
Cap/Base	G13
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC000108
Luminous flux (lm)	5200
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	840
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	Not applicable
Wattage (W)	58.00
Product Voltage (V)	110
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Average life (Nominal) (h)	20000
Product EAN number	5410288014944

DATA TABLE

General data

Product name	F58w/T8/840 Shatter-Proof Fep
Technology	Fluorescent
Watt (Rated) (W)	58.00
Lamp shape	Tube, double-ended
Type	T8 Luxline Plus FEP
Cap/Base	G13

T8 Luxline Plus FEP

F58w/T8/840 Shatter-Proof Fep
0001494

Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC000108

Optical data

Luminous flux (lm)	5200
Luminous flux (Rated) (lm)	5200
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	840
CRI (Ra)	85
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 2000 h 50Hz	0.96
Rated lumen maint. factor (%) at 4000 h 50Hz	0.94
Rated lumen maint. factor (%) at 6000 h 50Hz	0.92
Rated lumen maint. factor (%) at 8000 h 50Hz	0.91
Rated lumen maint. factor (%) at 12000 h 50Hz	0.90
Rated lumen maint. factor (%) at 16000 h 50Hz	0.89
Rated lumen maint. factor (%) at 20000 h 50Hz	0.87

Electrical data

Wattage (W)	58.00
Watt (Rated) - High frequency (W)	50.00
Current (A)	0.670
Product Voltage (V)	110
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Dimming method	Mains: leading / trailing edge
Drive current (mA)	670
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	68

Lifetime data

Average life (Nominal) (h)	20000
Average life (Rated) (h)	20000
Rated survival factor (%) at 2000 h 50Hz	0.99
Rated survival factor (%) at 4000 h 50Hz	0.98

T8 Luxline Plus FEP

F58w/T8/840 Shatter-Proof Fep
0001494

Rated survival factor (%) at 6000 h 50Hz	0.96
Rated survival factor (%) at 8000 h 50Hz	0.94
Rated survival factor (%) at 12000 h 50Hz	0.92
Rated survival factor (%) at 16000 h 50Hz	0.80
Rated survival factor (%) at 20000 h 50Hz	0.50

Physical data

Nominal Product Length (mm)	1500.0
Nominal Product Diameter (mm)	26
Max. Length base to base (mm) - A	1500.0
Length base to pin Min-Max (mm) - B	1504.7-1507.1
Max. Lamp Length (mm) - C/L	1514.2
Max. Lamp Diameter (mm) - D	28.0
Weight (kg)	0.2


Packaging

Single packaging type	Carton
Product EAN number	5410288014944
Packaging single length / height (cm)	151.1
Packaging single width (cm)	2.9
Packaging single depth (cm)	2.8
DUN14 (outer)	15410288014941
Units per outer package	25
Packaging outer length / height (cm)	154.5
Packaging outer width (cm)	15.5
Packaging outer depth (cm)	15.0

Safety data


Lamp mercury content (mg)	2.80
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	No
Suitable for household illumination	Yes

PHOTOMETRY




T8 Luxline Plus FEP
F58w/T8/840 Shatter-Proof Fep
0001494

TECHNICAL DRAWINGS



0001494



58
kWh/1000h




2019/2015

SYLVANIA

T8 Luxline Plus FEP
F58w/T8/840 Shatter-Proof Fep
0001494



0001494



58
kWh/1000h



2019/2015