

Self-locking threaded support bolt

Quick and easy-to-use attachment point

HALDER

Application:

For lifting loads. The threaded support bolt is inserted into a threaded hole and secures itself. In contrast to a ring screw, this eliminates time-consuming screwing and unscrewing.

Execution:

- Stop point with self-locking thread
- Shackles made of heat-treated steel, tempered, manganese phosphate-coated
- Stainless steel 1.4542 thread element, precipitation-hardened
- Movable shackle
- Loosen the safety bar to prevent accidental release
- High-strength, precipitation-hardened bolts
- Aluminium press stud
- TÜV tested - in accordance with DIN EN 13155

Advantage:

- Time savings of up to 95% compared to conventional ring bolts



Art. no.	77241 106
Brand	HALDER
Manufacturer Part Number	22352.0024
Thread dimension	M24
Load-carrying capacity	2300 kg
Material of shackles	Steel tempered
Surface of the shackle	Manganese phosphated
Material of bolt	Steel tempered
Material of spring	Corrosion resistant steel
Material of push knob	Aluminium
Weight	1167 g
Max. temperature	250 °C
Design	Self-locking
Operation	By pressing the button
With corrosion protection	Yes
Length to centre of bolt	27 mm
Bolt length	36 mm
Length 3	42 mm
Bolt length above	60 mm
Interior height	50.6 mm
Internal width	49.8 mm
External width	82 mm
Height	152 mm
Outer diameter	20.7 mm
Diameter bolt top	36 mm
Thread length	22 mm
Gross Weight	1.167 kg
Product Group	7EC

EAN

4030618715221