

PRODUCT-DETAILS

OT400E22P

OT400E22P SWITCH-DISCONNECTOR



General Information

Extended Product Type	OT400E22P
Product ID	1SCA022727R5830
EAN	6417019235707
Catalog Description	OT400E22P SWITCH-DISCONNECTOR
Long Description	4-pole, front operated, base mounted switch-diconnector with black IP65 handle and shaft, terminal bolt kit included

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85365080
Country of Origin	Finland (FI)

Popular Downloads

Data Sheet, Technical Information	1SCC301020C0201
Instructions and Manuals	1SCC301035M0019
Mechanical Drawings	1SCC301288F0001 1SCC301287F0001 OT315-400E22.igs

Dimensions

Product Net Width	240 mm
Product Net Height	185 mm
Product Net Depth / Length	107 mm
Product Net Weight	3.9 kg 8.5 lb

Technical

Rated Operational Current AC-21A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A (1000 V) 400 A
Rated Operational Current AC-22A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Current AC-23A (I_e)	(380 ... 415 V) 400 A (500 V) 400 A (690 V) 400 A
Rated Operational Power AC-23A (P_e)	(220 ... 240 V) 132 kW (400 ... 415 V) 230 kW (500 V) 280 kW (690 V) 400 kW
Conventional Free-air Thermal Current (I_{th})	q = 40 °C 400 A
Conventional Thermal Current (I_{the})	Fully Enclosed 400 A
Rated Impulse Withstand Voltage (U_{imp})	12 kV
Rated Insulation Voltage (U_i)	acc. to IEC/EN 60664-1 1000 V
Rated Operational Voltage	Main Circuit 1000 V
Rated Short-Circuit Making Capacity (I_{cm})	(690 V) 65 kA
Rated Short-time Withstand Current (I_{cw})	for 1 s 15 kA
Power Loss	at Rated Operating Conditions per Pole 10 W
Pollution Degree	3
Handle Color	Black
Handle Type	Handle and shaft included
Fourth Pole Position	Right Side
Fourth Pole Type	Switched - Simultaneous Function
Switches Operating Mechanism	Mechanism Between the Poles 22 (Between the Poles)
Distance Between Phases	Standard
Position of Line Terminals	Top In - Bottom Out Bottom In - Top Out
Operating Mode	Front operated
Standards	IEC 60947-3
Special Functions	No

Mounting Type	Base mounting
Number of Poles	4
Degree of Protection	Front IP00
Terminal Type	Lug terminals
Terminal Width	25 mm
Tightening Torque	acc. IEC 60947-1 30...44 N·m
Mechanical Durability	16000
Lock Type	Yes

Environmental

RoHS Status	Following EU Directive 2011/65/EU
Environmental Information	1SCC301149D0202

Certificates and Declarations (Document Number)

BV Certificate	1SCC301103D0201
Declaration of Conformity - CE	1SCC301135D2704
DNV GL Certificate	1SCC301174D0204
Environmental Information	1SCC301149D0202
GL Certificate	1SCC301139D0201
Instructions and Manuals	1SCC301035M0019
LR Certificate	1SCC301144D0201
RoHS Information	1SCC301149D0203

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	220 mm 8.7 in
Package Level 1 Depth / Length	260 mm 10.2 in
Package Level 1 Height	155 mm 6.1 in
Package Level 1 Gross Weight	4.2 kg 9.3 lb
Package Level 1 EAN	6417019235707

Classifications

Object Classification Code	Q
ETIM 5	EC000216 - Switch disconnecter
ETIM 6	EC000216 - Switch disconnecter
ETIM 7	EC000216 - Switch disconnecter
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
E-Number (Finland)	3661456

Categories

Low Voltage Products and Systems → Switches → Switch Disconnectors

