PHILIPS Lighting



G ^A

MASTER LEDspot ExpertColor MV

MAS LED ExpertColor 3.9-35W GU10 927 25D

MASTER LEDspot ExpertColor creates a warm and comfortable ambience for hospitality venues, homes and restaurants. They offer superior lighting that has a customized spectrum, high CRI, and deep dimming feature. What's more the innovative, trimless lens design will also suit almost any interior decor with its clean and neat look. In addition, with MASTER LEDspot ExpertColor you can take advantage of the full ExpertColor family, which also includes LEDspot MR16, LEDspot AR111 and LEDspot PAR lamps. MASTER LEDspot ExpertColor delivers huge energy savings and minimizes maintenance costs without any compromise on light quality and lifetime, enabling residential and business owners to achieve a return on their investment within a short time period.

Product data

| GU10 [GU10] |
|-----------------|
| 40,000 hour(s) |
| 50,000 |
| LED |
| Narrow Cone |
| |
| |
| 927 |
| 25 degree(s) |
| 265 lumen |
| 700 cd |
| Warm White (WW) |
| 2700 K |
| 67.95 lm/W |
| |


| Color Consistency | <3 |
|---------------------------------------|-------------|
| Color rendering index (CRI) | 97 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % |
| Luminous Flux in 90° Cone (Rated) | 265 lumen |
| | |
| Operating and Electrical | |
| Line Frequency | 50 to 60 Hz |
| Input Frequency | 50 to 60 Hz |
| Power Consumption | 3.9 W |
| Lamp Current (Nom) | 22 mA |
| Wattage Equivalent | 35 W |
| Starting Time (Nom) | 0.5 s |
| Warm-up time to 60% light | 0.5 s |
| Power Factor (Fraction) | 0.8 |
| | |

MASTER LEDspot ExpertColor MV


| Voltage (Nom) | 220-240 V |
|-------------------------------|----------------------------|
| | |
| Temperature | |
| T-Case Maximum (Nom) | 2° 08 |
| | |
| Controls and Dimming | |
| Dimmable | Only with specific dimmers |
| | |
| Mechanical and Housing | |
| Bulb Shape | PAR16 [PAR 2 inch/50mm] |
| | |
| Approval and Application | |
| Energy Efficiency Class | G |
| Suitable For Accent Lighting | Yes |
| Energy Consumption kWh/1000 h | 4 kWh |

| EPREL Registration Number | 544215 |
|---------------------------------|--|
| CE mark | Yes |
| EU RoHS compliant | Yes |
| | |
| Product Data | |
| Full product code | 871869670749400 |
| Order product name | MAS LED ExpertColor 3.9-35W GU10 927 25D |
| Order code | 929001346402 |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 10 |
| Material number (12NC) | 929001346402 |
| Full product name | MAS LED ExpertColor 3.9-35W GU10 927 25D |
| EAN/UPC - Case | 8718696707500 |

Dimensional drawing




Photometric data



Accent Lighting Spots - MAS LED ExpertColor 3.9-35W GU10 927 25D

| Product | D | с |
|--|-------|-------|
| MAS LED ExpertColor 3.9-35W GU10 927 25D | 50 mm | 54 mm |




Spectral Power Distribution Colour - MAS LED ExpertColor 3.9-35W GU10 927 25D

Datasheet, 2023, June 2


MASTER LEDspot ExpertColor MV

Photometric data




Light Distribution Diagram - MAS LED ExpertColor 3.9-35W GU10 927 25D

Lifetime



Life Expectancy Diagram - MAS LED ExpertColor 3.9-35W GU10 927 25D



Lumen Maintenance Diagram - MAS LED ExpertColor 3.9-35W GU10 927 25D



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.