





**HACC**

High SRF



Part No	Inductance	f <sub>L</sub>	Tol	Q	f <sub>Q</sub>	SRF <sub>min</sub>	DCR <sub>max</sub>	Rated DC
	L (µH)	(MHz)	± (%)	min	(MHz)	(MHz)	(Ω)	Current (A)
HACC-4R7X-YY	4.7	1	<b>10,20</b>	50	7.96	60	0.17	1.30
HACC-5R6X-YY	5.6	1	<b>10,20</b>	50	7.96	45	0.19	1.25
HACC-6R8X-YY	6.8	1	<b>10,20</b>	40	7.96	35	0.22	1.20
HACC-8R2X-YY	8.2	1	<b>10,20</b>	40	7.96	25	0.24	1.15
HACC-100X-YY	10	1	<b>10,20</b>	40	2.52	21	0.25	1.10
HACC-120X-YY	12	0.02	<b>10,20</b>	35	2.52	17	0.27	1.05
HACC-150X-YY	15	0.02	<b>10,20</b>	35	2.52	16	0.30	1.00
HACC-180X-YY	18	0.02	<b>10,20</b>	35	2.52	15	0.33	0.95
HACC-220X-YY	22	0.02	<b>10,20</b>	35	2.52	13	0.37	0.90
HACC-270X-YY	27	0.02	<b>10,20</b>	35	2.52	11	0.42	0.85
HACC-330X-YY	33	0.02	<b>10,20</b>	35	2.52	11	0.54	0.65
HACC-470X-YY	47	0.02	<b>10,20</b>	35	2.52	11	0.90	0.60
HACC-102X-YY	1000	0.79	<b>10,20</b>	60	0.79	2.8	18.0	0.12

Core Material : Ferrite

Revision date : 11 Aug 2014

SPQ :

Packing Form	Taped / Reel	Taped / Ammopack
Axial	-	1200 [-02]
Radial	1500 [-31]	1000 [-32]