



weekly time switch, mini dig. 230V AC, 1 channel, 1MW

Model	
product brand name	SETRON
product designation	Digital time switch
design of the product	Mini
design of the switching function	NO contact
General technical data	
principle of operation	
• radio-controlled	No
• line-synchronous	No
• quartz-controlled	No
accuracy per day	1 s
shortest switching time interval of channel 1	60 s
Voltage	
control voltage at AC rated value	
• minimum	250 V
• maximum	250 V
overvoltage category according to IEC 61010-1	III
Supply voltage	
operating voltage at AC rated value	250 V
type of voltage of the supply voltage	AC
supply voltage frequency maximum	60 Hz
Protection class	
protection class IP	IP20
Switching capacity	
switching capacity current at AC at 250 V rated value	16 A
Product function	
product function	
• 60 min time program	Yes
• Astro program	No
• automatic daylight-saving adjustment	Yes
• operating hours counter	No
• direct operation	Yes
• holiday time program	No
• pulse program	No
• annual time program	No
• switching preselection	Yes
• 24 hr time program	Yes
• text guidance in display	Yes
• weekly time program	Yes
• random time program	No

• cyclical time program	No	
Number		
number of terminals with cross-head screw	1	
number of channels	1	
number of memory slots	28	
connectable conductor cross-section in main circuit		
• for rigid conductor maximum	4 mm ²	
• for rigid conductor minimum	1.5 mm ²	
• for flexible conductor with core end processing maximum	2.5 mm ²	
Mechanical Design		
height	83 mm	
width	18 mm	
depth	64 mm	
number of modular width units	1	
fastening method	DIN rail	
Environmental conditions		
ambient temperature during operation		
• minimum	-20 °C	
• maximum	55 °C	
ambient temperature during storage		
• minimum	-20 °C	
• maximum	60 °C	
General Product Approval	Declaration of Conformity	other

[Confirmation](#)



[Confirmation](#)

other	Dangerous Good	Environment
Miscellaneous	Dangerous Goods Information	Environmental Conformations

Further information

Siemens has decided to exit the Russian market (see here).
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.
 Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=7LF4501-5>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
<https://support.industry.siemens.com/cs/ww/en/ps/7LF4501-5>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=7LF4501-5

CAX-Online-Generator
<http://www.siemens.com/cax>

Tender specifications
<http://www.siemens.com/specifications>

last modified: 2/8/2023

