



## Alcoswitch | Alcoswitch Gemini A Series

TE Internal #: 4-1825136-9

Alcoswitch Gemini A Series, Toggle Switches, Single Pole - Double Throw Configuration (Pole-Throw), 1/4-40, Sealed Toggle Switch, Copper, Silver

[View on TE.com >](#)
[Relays, Contactors & Switches > Switches > Toggle Switches](#)
Configuration (Pole-Throw): **Single Pole - Double Throw**Bushing Thread Size: **1/4-40**Sealed Toggle Switch: **Yes**Contact Base Material: **Copper**Switch Contact Plating Material: **Silver**

## Features

### Product Type Features

|                      |            |
|----------------------|------------|
| Product Type         | Switch     |
| Sealed Toggle Switch | Yes        |
| Toggle Style         | Baton Long |
| Toggle Switch Type   | Toggle     |
| Toggle Actuation     | Vertical   |

### Configuration Features

|                            |                            |
|----------------------------|----------------------------|
| Configuration (Pole-Throw) | Single Pole - Double Throw |
| Operating Function         | On On                      |

### Electrical Characteristics

|                              |                 |
|------------------------------|-----------------|
| Dielectric Strength          | 1000 VAC        |
| Insulation Resistance        | 1000 MΩ         |
| Contact Resistance           | 10 mΩ           |
| Toggle Switch Voltage Rating | 125 VAC, 28 VDC |

### Body Features

|                         |                       |
|-------------------------|-----------------------|
| Actuator Finish         | Nickel                |
| Bushing Thread Size     | 1/4-40                |
| Toggle Switch Seal Type | Terminal Seal (Epoxy) |
| Bushing Style           | Threaded              |



### Contact Features

|                                      |        |
|--------------------------------------|--------|
| Contact Base Material                | Copper |
| Switch Contact Plating Material      | Silver |
| Toggle Switch Contact Current Rating | 5 A    |

### Termination Features

|                  |           |
|------------------|-----------|
| Termination Type | Wire Lugs |
|------------------|-----------|

### Mechanical Attachment

|                             |        |
|-----------------------------|--------|
| Toggle Switch Mounting Type | Solder |
|-----------------------------|--------|

### Housing Features

|                |    |
|----------------|----|
| Process Sealed | No |
|----------------|----|

### Dimensions

|               |                           |
|---------------|---------------------------|
| Toggle Length | 10.4 mm[.41 in]<br>.35 in |
|---------------|---------------------------|

### Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-1 |
|------------------------|----------|

## Product Compliance




[For compliance documentation, visit the product page on TE.com>](#)

|   |   |
|---|---|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions   |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions   |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold  |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JAN 2021 (211)<br>SVHC > Threshold:<br>Pb (4% in Component)<br><b>Article Safe Usage Statements:</b><br>Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free   |
| Solder Process Capability                     | Wave solder capable to 265°C  |

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts









Also in the Series | **Alcoswitch Gemini A Series**



Customers Also Bought





## Documents

### Product Drawings

[A101SYZQ04](#)

English

---

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1825136-9\\_A.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1825136-9\\_A.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1825136-9\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

### Datasheets & Catalog Pages

[SWITCHES\\_CORE\\_PROGRAM\\_CATALOG](#)

English

[GEMINI\\_SERIES\\_SWITCHES\\_QUICK\\_REF\\_GUIDE\\_2-1773458-5](#)

English