

Power PCB Relay RT1 Inrush

- 1 pole 16A, 1 form C (CO) or 1 form A (NO) contact
- For inrush peak currents up to 80A
- Mono- or bistable coil
- 5kV/10mm coil-contact
- **■** Reinforced insulation
- Ambient temperature 85°C

Typical applications
Domestic appliances, heating control, lighting control



F0177-C




Approvals
VDE REGNr. 6106, cULus E214025, cCSAus 14385
Technical data of approved types on request


Contact Data	
Contact arrangement	I form C (CO) or 1 form A (NO)
Rated voltage	250VAC
Max. switching voltage	400VAC
Rated current	16A
Limiting continuous current	16A, UL: 20A (K-version)
Limiting making current,	
max. 4s, df 10%	30A
max. 20ms (incandescent lamps), RT3	3L version 80A
Breaking capacity max.	4000VA
Contact material	AgNi90/10, AgSnO
Frequency of operation, with/without loa	ad 360/72000h ⁻¹
Operate/release time max., DC coil	9/6ms
Operate/Reset time max., bistable version	on 10/10ms
Bounce time max., form A/form B	3/6ms

Contact	ratings		
Туре	Contact	Load	Cycles
IEC 6181	0		
RT33L	A (NO)	16A, 250VAC resistive, 85°C	$50x10^3$
RT33K	A (NO)	16A, 250VAC resistive, 85°C	$30x10^3$
UL 508			
RT33K	A (NO)	20A, 277VAC general purpose, 40°C	10x10 ³
RT33L	A (NO)	16A, 277VAC resistive, 85°C	$50x10^3$
RT33L	A (NO)	1000W Tungsten, 120VAC, 60 Hz, 40°C	6x10 ³
RT33L	A (NO)	1000W standard ballast,	
		120VAC, 60 Hz, 40°C	6x10 ³

Mechanical endurance monostable version bistable version

>30x106 operations >5x106 operations






Coil Data, DC coil		
Coil voltage range	5 to 110VDC	
Operative range, IEC 61810	2	
Coil insulation system according UL	class F	

Coil vers	sions, DC co	il			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance	power
	VDC	VDC	VDC	$\Omega \pm 10\%^{1)}$	mW
005	5	3.5	0.5	62	403
006	6	4.2	0.6	90	400
012	12	8.4	1.2	360	400
024	24	16.8	2.4	1440	400
048	48	33.6	4.8	5520	417
060	60	42.0	6.0	8570 ¹⁾	420

1) Coil resistance ±12%.

All figures are given for coil without pre-energization, at ambient temperature $+23^{\circ}$ C. Other coil voltages on request.



Coil Data, bistable coils	1 coil	2 coils
Magnetic system	polarize	d, bistable
Coil voltage range	5 to	24VDC
Operative range, IEC 61810		2
Limiting voltage, % of rated coil volt	age 120%	150%
Min./Max. energization duration	30ms/1min at	<10% duty factor
Coil insulation system according UL	. cla	ass F



Power PCB Relay RT1 Inrush (Continued)

Coil Da	ita (continued	d)					
Coil versions, bistable coil							
Coil	Rated	Set	Reset	Coil	Rated coil		
code	voltage	voltage	voltage	resistance	power		
	VDC	VDC	VDC	Ω±10%	mW		
bistable,	, 1 coil						
A05	5	3.5	2.8	62	403		
A06	6	4.2	3.3	90	400		
A12	12	8.4	6.6	360	400		
A24	24	16.8	13.2	1440	400		
bistable	, 2 coils						
F05	5	3.5	2.8	42	595		
F06	6	4.2	3.3	55	655		
F12	12	8.4	6.6	240	600		

13.2 All figures are given for coil without pre-energization, at ambient temperature +23°C. Other coil voltages on request

16.8

Bistable coils - operation


F24


24

Version	1 coil		2 coils
Coil terminals	A1	A2	A1 A3 A2
Operate	+	-	+ -
Reset	-	+	- +
Contact position not defined at delivery			

886

650





Insulation Data	
Initial dielectric strength	
between open contacts	1000V _{rms}
between contact and coil	5000V _{rms}
Clearance/creepage	
between contact and coil	≥10/10mm
Material group of insulation parts	IIIa
Tracking index of relay base	PTI 250V

Other Data

Material compliance: EU RoHS/ELV, China RoHS, REACH, Halogen content refer to the Product Compliance Support Center at www.tycoelectronics.com/customersupport/rohssupportcenter

,,	
Ambient temperature	-40 to 85°C
Category of environmental protection	
IEC 61810	RTII - flux proof
Vibration resistance (functional),	
form A/form B contact, 30 to 500Hz	20/5g
Shock resistance (destructive)	100g
Terminal type	PCB-THT, plug-in ²⁾
Weight	14g
Resistance to soldering heat THT	
IEC 60068-2-20	270°C/10s
Packaging/unit	tube/20 pcs., box/500 pcs.


2) socket available for 1 coil version only, see Accessories

Accessories

Accessories Industrial Power Relay RT²⁾ For details see datasheet Socket available for 1 coil version only.

NOTE: indicated contact ratings and electrical endurance data for direct wiring of relays (according IEC 61810-1); for relays mounted on sockets deratings may apply.

Dimensions






Power PCB Relay RT1 Inrush (Continued)


PCB layout / terminal assignment

Bottom view on solder pins


16A, 1 form C (CO) contact, pinning 5mm



monostable version




bistable version a)




20162 D






monostable version




bistable version a)



- a) Indicated contact position during or after coil energization with reset voltage.
- b) for 2 coil version only

 $^{\ast}\!)$ With the recommended PCB hole sizes a grid pattern from 2.5mm to 2.54mm can be used.



Product code	Version	Contact material	Coil version	Coil	Part number
RT31L012	1 form A (NO)	AgSnO ₂	Monostable	12VDC	7-1393239-3
RT31L024	16A			24VDC	7-1393239-5
RT31L048	pinning 5mm			48VDC	7-1393239-6
RT33K012	flux proof	AgNi 90/10		12VDC	2-1393240-3
RT33K024				24VDC	2-1393240-4
RT33KF12			Bistable 2 coils	12VDC	1-1415540-1
RT33L012		AgSnO ₂	Monostable		3-1393240-3
RT33L024				24VDC	3-1393240-5
RT33LA12			Bistable 1 coil	12VDC	2-1393240-7
RT33LA24				24VDC	3-1415379-1

This list represents the most common types and does not show all variants covered by this datasheet. Other types on request