

Cutter for circular cutter, type 6

Application:

For use in a circular cutter, type 00 and 00a, for cutting plastics such as hard PVC, Plexiglas, polyamide with a max. cutting depth of 15 mm on one side. For two-sided machining, max. cutting depth of 30 mm.



Art. no.	11373 160
Brand	GFS
Manufacturer Part Number	22 011 126
Form	6
Suitable for type	00, 00 a
Cutting material	Carbide
Surface	Uncoated
Gross Weight	0.009 kg
Product Group	119