

## Fixed centring point

Carbide-tipped point

**ORION**<sup>®</sup>

### Application:


For centring and supporting long and narrow workpieces on lathes and grinding machines.

### Execution:

- Tip angle 60°.
- Carbide-tipped.
- Precision-ground.

### Advantage:

- Wear-resistant carbide tip.



|                                 |                  |
|---------------------------------|------------------|
| <b>Art. no.</b>                 | <b>22107 040</b> |
| <b>Brand</b>                    | ORION            |
| <b>Manufacturer Part Number</b> | 22107040         |
| <b>Morse taper size</b>         | MK 4             |
| <b>Programming size</b>         | 57.5 mm          |
| <b>Diameter of flat area</b>    | 14 mm            |
| <b>Outer diameter</b>           | 31.6 mm          |
| <b>DIN</b>                      | 806              |
| <b>Gross Weight</b>             | 0.800 kg         |
| <b>Product Group</b>            | 211              |

### EAN

4039247140060