

## CP7737 pneumatic angled impact screwdriver

Loosening torque 300 Nm



### Application:

supplies maximum torque in restricted spaces

### Execution:

- motor installed in the head of the impact screwdriver for greater power directly at the point of impact
- Ergonomic handle coated with plastic fits perfectly in hand
- Sturdy aluminium housing

### Advantage:

- no energy losses through gear unit and improved air consumption
- Full control thanks to fine-tuned printer
- Easy to use: Change of rotation direction with one hand
- Durable (Jumbo hammer impact mechanism, steel engine, composite coating)
- Work for longer without signs of fatigue



<b>Art. no.</b>	<b>75066 045</b>
<b>Brand</b>	CP
<b>Manufacturer Part Number</b>	8941077370
<b>Model</b>	CP7737
<b>Max. tightening torque</b>	224 Nm
<b>Max. releasing torque</b>	300 Nm
<b>Max. idle speed</b>	9000 rpm
<b>Air consumption</b>	7.5 l/min
<b>Tool holding device</b>	1/2-inch external square
<b>Hammer mechanism system</b>	Jumbo hammer mechanism
<b>Length</b>	240 mm
<b>Housing width</b>	60 mm
<b>Connection thread</b>	G 1/4 inch
<b>Inner hose diameter</b>	10 mm
<b>Sound-pressure level</b>	93
<b>Weight</b>	1.13 kg
<b>With right/left-hand rotation</b>	Yes
<b>Gross Weight</b>	1.384 kg
<b>Product Group</b>	752

### EAN

0015451761158