

Column-mounted slewing jib crane MEISTER M – complete set with compound anchor system and chain hoist

The world's most popular crane in its class



Application:

Proven crane with a particularly wide range of applications. Perfect for halls/rooms with low ceilings.

Execution:

- Classification according to EN 13001 HC2 S3 HD2 for medium industrial use
- power supply with round trailing cable
- lockable isolating switch
- 400 V/50 Hz, control voltage: 24 V
- Electric chain hoist with manual sliding chassis – two-stage lifting speed
- Swivel range 360°
- **WITH DÜBEL MOUNTING SYSTEM VAS2 (simple installation and no foundation required)**



Advantage:

- Proven 100,000 times
- Particularly wide range of applications
- Ideal for halls/rooms with low ceilings
- Cost-effective to assemble and rapid to commission thanks to a compound anchor system (no foundation or bottom casting)

Delivery:

Incl. detailed documentation

Art. no.	77111 059
Brand	VETTER
Manufacturer Part Number	M1,25-3,0+SIXX1F-HF
Load-carrying capacity	125 kg
Overhang	3000 mm
Construction height	3550 mm
Model	MEISTER M
Lower edge of crane bottom	3300 mm
Max. lift height	2867 mm
Lifting device design	With electric chain hoist SIXX-HF
Mounting plate diameter	530 mm
Design	With electric chain hoist and VAS2
Height of hoist	433 mm
Stroke speed of precision hoist	2 m/min
Stroke speed of main hoist	8 m/min
Flange width	91 mm
Surface	Lacquered
Weight	337 kg
Operating voltage	400 V
Swivel range	360 Degree
Colour	Daffodil yellow RAL 1007
Max. vertical force	4 kN
Product category	B2B produkt
Gross weight	413 kg
Made in	Germany
Gross Weight	413.000 kg
Product Group	7EL