


Image for reference only

### Features:

- A range of step-up/step-down auto-transformers 0-110-220-230-240V, 50/60Hz.
- Power ratings 100 ~ 5000VA
- Connection made by insulated terminal block
- Windings are covered with metal shrouds
- Insulating rating: Class B



\*Note:  
50VA has voltages  
0-115-230

Schematic for reference

Auto-transformers are suitable for applications where mains isolation is not essential.

The short term VA is indicated for applications of a intermittent load, generally for applications with an average intermittent work load of 50% . Example: supply to fridges, air conditioners, compressors etc..

Other ratings and voltages can be supplied on request.

Part No.	VA Rating	VA Max Short term	Dimension (mm)					Weight Kgs
			A	B	C	D	E	
<b>VTX-186-50*</b>	<b>50</b>	<b>50</b>	67	83	75	57	44	0.7
<b>VTX-186-100</b>	<b>100</b>	<b>100</b>	65	96	77	57	44	1.4
<b>VTX-186-150</b>	<b>150</b>	<b>150</b>	65	96	77	57	44	1.4
<b>VTX-186-200</b>	<b>200</b>	<b>300</b>	74	123	78	60	58	2.1
<b>VTX-186-250</b>	<b>250</b>	<b>300</b>	74	123	78	60	58	2.1
<b>VTX-186-300</b>	<b>300</b>	<b>450</b>	83	129	100	66	66	3
<b>VTX-186-500</b>	<b>500</b>	<b>750</b>	83	144	100	66	81	3.6
<b>VTX-186-1000</b>	<b>1000</b>	<b>1500</b>	103	166	124	81	92	6.3
<b>VTX-186-2000</b>	<b>2000</b>	<b>3000</b>	128	192	154	101	106	10.5
<b>VTX-186-3000</b>	<b>3000</b>	<b>4500</b>	128	202	154	101	116	13.5
<b>VTX-186-5000</b>	<b>5000</b>	<b>7500</b>	164	210	197	128.5	108	20

Products can be altered to suit custom requirements. Please contact Vigortronix for your specific requirements.  
The information contained in this document is subject to change without notice.