

## MSUD VALVE PLUG FORM A ,CAPACITY REDUCER -60%

PUR 3X0.75 black UL/CSA, drag ch 3m

Power reducer (60 %)  
Valve Connectors  
Form A (18 mm)  
24 V DC  
LED (yellow)

Further cable lengths on request. Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Form

18221

#### Technical Data

Operating voltage	21.6...26.4 V DC
Operating current per contact	max. 5 A
Locking of ports	M3 (recommended torque 0.4 Nm)
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Housing	Black plastic (gray on request)
Frequency	max. 1 Hz
Switching time	max. 200 ms
Operating frequency	300...500 Hz

#### Cables

Cable number	636
No./diameter of wires	3 × 0.75 mm <sup>2</sup>

Wire isolation	PP (bk, num, gnye)
C-track properties	5 Mio.
Torsion	2 Mio. $\pm$ 180°/m
Jacket Color	black
Shore hardness outer jacket	90 $\pm$ 5A
Material (jacket)	PUR (UL/CSA)
Outer diameter	approx. 5.9 mm
Bend radius (fixed)	5 $\times$ outer $\varnothing$
Bend radius (moving)	10 $\times$ outer $\varnothing$
Temperature range (fixed)	-40...+80 °C
Temperature range (mobile)	-25...+80 °C

#### Commercial data

country of origin	CZ
customs tariff number	85444290
minimum order quantity	1