

## Product information

# 13 66 180 T

### KNIPEX StriX®

Insulation strippers with cable shears

IEC 60900 DIN EN 60900



⚡ 1000 V



**Wire stripper with integrated cable shears: clean, crush-free cutting and damage-free stripping with just one pair of pliers**

- Wire stripper with cable shears – two essential electrical installations tools in one pair of pliers
- Pliers with integrated, insulated tether attachment point for a tool tether
- Integrated cable shears for the clean cutting of Cu- and Al-cables without crushing
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 57 HRC
- Universal adjustment of the stripping blades by means of a knurled screw
- Slim dimensions for easy access
- Stripping of single-, multi- and fine stranded conductors with plastic or rubber insulation up to Ø 5 mm or 10 mm<sup>2</sup> cross-section
- Graduated jaw provides a visual orientation aid when stripping wire in standard lengths (11 mm and 16 mm)
- High-grade special tool steel, forged, multi stage oil-hardened

## General

Article No.	13 66 180 T
EAN	4003773081906
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
Weight	216 g
Dimensions	180 x 53 x 27 mm
Standard	DIN EN 60900 IEC 60900
Reach	no
RohS	no

## Technical details

Cutting capacity copper cable, multiple-stranded	50 mm <sup>2</sup>
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
Stripping capacities in square millimetres	10.0 mm <sup>2</sup>
Stripping capacities (diameter)	Ø 5.0 mm
AWG	8
Drop Protection System	yes
VDE tested	yes

## Classification

eCl@ss 5.1.4	21040302
ETIM 5.0	EC000163
ETIM 6.0	EC000163
proficl@ss 6.0	AAA002c003
UNSPSC 13.1	27111506

*technical change and errors excepted*

