

INSERTABLE PROFILE, FOR 95MM<sup>2</sup> TERMINALS,  
COMPENSATES PRISMATIC SLEEVE BASES WHEN  
STRIP LINES ARE USED



Figure similar

General technical data		
Insulation material		others
Protection class		
Combustibility class acc. to UL 94		others
Appearance		
Color		miscellaneous
Product details		
Product component / required / connection plate		No
Number		
Number of terminal points / per terminal level		0
Connections		
Connectable conductor cross-section		
<ul style="list-style-type: none"> <li>• finely stranded</li> <li>— with core end processing / minimum</li> <li>— with core end processing / maximum</li> </ul>	mm <sup>2</sup> mm <sup>2</sup>	25 95
Type of electrical connection		
<ul style="list-style-type: none"> <li>• 1</li> <li>• 2</li> </ul>		Miscellaneous Miscellaneous
Position / of the terminal		lateral
Mechanical Design		
Height / with lowest-profile installation	mm	81.5
Mounting type		others

## Environmental conditions

### Ambient temperature

- |                              |    |     |
|------------------------------|----|-----|
| • during operation / minimum | °C | -25 |
| • during operation / maximum | °C | 35  |

### General Product Approval

### Declaration of Conformity



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WH90203NA00>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8WH90203NA00/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8WH90203NA00](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8WH90203NA00)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015