


## Start Waterproof LED G3 GRP body

START Waterproof GRP Twin 1500 IP65 7100lm 840  
0068068



### Product features

- Start Waterproof, integrated LED weatherproof luminaire, with UV stabilized flat diffuser and linear prisms designed to achieve uniform lit appearance, optimise light output and to reduce glare, 301 stainless steel diffuser clips and fixing brackets for surface mounting. Glass Reinforced Plastic housing for robustness, Polycarbonate diffuser, 7050 lm, 58 W, 122 lm/W, 4000 K, drive current 700 mA, Non dimmable, CRI80, IP65, IK08, Class I, nominal average life (h):50000, 1578 mm x 110 mm x 78 mm ,energy class: A++ A+ A, D-mark



### PRODUCT OVERVIEW

Product name	START Waterproof GRP Twin 1500 IP65 7100lm 840
Technology	LED
Housing	Composite material
Mount	Ceiling surface mounting
Fixture rating	Enclosed
General application	Logistics & Industry
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	7050
Luminaire efficacy (lm/W)	122
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Photobiological Risk Group	RG0
Total power consumption (W)	58
Electrical protection	Class I
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Housing colour	Grey
IP rating	IP65
IK rating	IK08
Product EAN number	5410288680682

### DATA TABLE

#### General data

Product name	START Waterproof GRP Twin 1500 IP65 7100lm 840
Technology	LED
Housing	Composite material
Mount	Ceiling surface mounting
Fixture rating	Enclosed

## Start Waterproof LED G3 GRP body START Waterproof GRP Twin 1500 IP65 7100lm 840 0068068

General application	Logistics & Industry
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	7050
Luminaire efficacy (lm/W)	122
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Photobiological Risk Group	RG0

### Electrical data

Total power consumption (W)	58
Mains voltage (V)	220-240V
Lamp power factor	1
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class I
Control gear required	No
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Drive current (mA)	700
Inrush Current (A)	15
Inrush Duration (µs)	50
Glow Wire Test (°C)	850
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	25
Max. Luminaires per 13A C Breaker	35
Max. Luminaires per 16A C Breaker	40
Max. Luminaires per 20A C Breaker	50
Max. Luminaires per 10A B Breaker	25
Max. Luminaires per 13A B Breaker	30
Max. Luminaires per 16A B Breaker	40
Max. Luminaires per 20A B Breaker	50

### Lifetime data

Lifespan L70 B50	60000
Lifespan L70 B20	60000
Lifespan L70 B10	60000
Lifespan L80 B50	60000
Lifespan L80 B20	60000
Lifespan L80 B10	60000
Lifespan L90 B50	59000
Lifespan L90 B20	53000
Lifespan L90 B10	50000

## Start Waterproof LED G3 GRP body

START Waterproof GRP Twin 1500 IP65 7100lm 840  
0068068

### Physical data

Housing colour	Grey
IP rating	IP65
IK rating	IK08
Diffuser finish	Transparent
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1578
Nominal Product Width (mm)	110
Nominal Product Height (mm)	78
Weight (kg)	2.64


### Packaging

Single packaging type	Carton
Product EAN number	5410288680682
Packaging single length / height (cm)	167.2
Packaging single width (cm)	11.6
Packaging single depth (cm)	8.4
DUN14 (outer)	05410288680682
Units per outer package	1
Packaging outer length / height (cm)	167.2
Packaging outer width (cm)	11.6
Packaging outer depth (cm)	8.4

### Safety data

Optimal operating condition (°C)	-20-40
Dry applications use only	No

## PHOTOMETRY



## TECHNICAL DRAWINGS

## Start Waterproof LED G3 GRP body *START Waterproof GRP Twin 1500 IP65 7100lm 840* 0068068

---

