

<b>Art. No.</b>	<b>23335 225</b>
<b>Tool holding device</b>	SK 40
<b>Overall length</b>	Ultra short
<b>Clamping diameter</b>	20 mm
<b>Projecting length</b>	24.5 mm
<b>Form</b>	AD/AF
<b>Outer diameter</b>	48 mm
<b>Diameter</b>	34 mm
<b>Max. adjustment travel</b>	10 mm
<b>Included in delivery</b>	Tool holder with matching hex key
<b>Coolant supply</b>	Internal axial/internal radial
<b>Suitable for thread</b>	M16 x 1
<b>Width across flats</b>	8 mm
<b>Balancing quality</b>	G 2.5 at 25 rpm
<b>Concentricity tolerance</b>	0.003 mm

**EAN-Code**

4050293349252