

PTGN clamp holder, left

For copy turning and longitudinal turning using TN indexable insert

ATORN®

Application


For copy turning and longitudinal turning using TN indexable insert 60°

Version

- precision-engineered steel support, burnished, hardened, toggle clamp system, type T, 90° pitch angle, 60° tip angle, 0° clearance angle

Advantage

- three-edge geometry lowers costs per cut
- negative body geometry ensures good stability and absorption of force for large cutting depths
- wide range of delivery: suitable for both finishing and roughing



Art. No.	17839 036
ISO name	PTGN R/L 2525 M16
Shaft height	25 mm
Shank width	25 mm
Length	150 mm
Length of head	22 mm
Programming size	32 mm
Suitable for indexable inserts	TN.. 1604..
Tool design	Left
DIN	4983

EAN-Code

4050293126884