

## VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

## DSO-2072H HANDHELD OSCILLOSCOPE



Item no: 2380256

The product is a battery operated 3 in 1 - Oscilloscope, multimeter and waveform generator. It has an 8.89 cm LCD color screen (320 x 240 pixels) and USB Type-C™ interface.

### FEATURES

#### Oscilloscope:

70 MHz bandwidth , 2 channels // Max. 250 MSa/s sampling rate // Max. 8K record length // 8-bit vertical resolution

#### Multimeter:

CATIII 1000 V // 20,000 Counts // Auto-range // TRMS // Measuring type - Voltage, current, resistance, capacitance, on/off, diode

#### Waveform generator:

Max. 25 MHz frequency output, 1 channel // Max. 125 MSa/s sampling rate // 0.1 Hz frequency resolution // 14-bit vertical resolution // 8K waveform length

### TECHNICAL DATA

#### Oscilloscope

Characteristics	Description
Bandwidth	70 MHz
Channel	2
<b>Sampling</b>	
Sampling method	Sampling, peak detection
Real-time sampling rate	125 MSa/s (Dual channel) 250 MSa/s (Single channel)
Waveform refresh rate	10,000 wfms/s
<b>Input</b>	
Input coupling	DC, AC, ground
Input impedance (DC coupling)	1 MΩ ±2 %, in parallel with 16 pF±10 pF



Characteristics		Description
Probe attenuation		1x, 10x, 100x, 1000x, 10000x
Maximum input voltage		400 V (DC + AC, PK - PK)
Bandwidth limit		20 MHz, Full bandwidth
<b>Horizontal</b>		
Sampling rate range		0.25 Sa/s - 250 MSa/s
Waveform interpolation		(Sinx)/x
Sweep speed range (S/div)		5ns/div - 1000s/div, Stepping in the 1-2-5 way
Time base accuracy		±100 ppm
Record length		8K or 4K optional
<b>Vertical</b>		
Sensitivity (Volt/div) range		10 mV/div - 10 V/div
Displacement range		±6 div
Analog bandwidth		70 MHz
Single bandwidth		Full bandwidth
Low frequency response (AC coupling, -3dB)		≥10 Hz
Rise time (typical on BNC)		≤ 5 ns
DC gain accuracy		3 %
<b>Measurement</b>		
Cursor		ΔV, ΔT
Automatic		Period, Frequency, Mean, PK-PK, Max, Min, Amplitude
<b>Triggering</b>		
Source		CH1, CH2
Type		Edge
Coupling		DC, AC
Trigger type		Auto, normal, single
Trigger electrical level range		±4 divs from the center of the screen
Trigger electrical level accuracy		±0.3 div
Edge triggering	Slope	Rising edge, falling edge

#### Probe compensator output

Characteristics		Description
Output voltage (typical)		3.3 Vpp, High-Z
Frequency (typical)		Square wave 1 kHz (±1 %)

#### Multimeter

Characteristics		Description
Digital display		20,000 readings
Measurement type		Voltage, current, resistance, capacitance, on/off, diode
Maximum input voltage		AC: 750 V/DC: 1000 V
Maximum input current		AC: 10 A/DC: 10 A

Range	Minimum resolution	Accuracy
<b>DC voltage</b>		
200.00 mV	0.01 mV	±(0.43 % +14dig)
2.0000 V	0.1 mV	±(0.43 % +7 dig)
20.000 V	1 mV	
200.00 V	0.01 V	
1000.0 V	0.1 V	±(0.71 % +7 dig)
<b>AC voltage</b>		
200.00 mV	0.01 mV	±(1.14 % +14 dig)

Range	Minimum resolution	Accuracy
2.0000 V	0.1 mV	
20.000 V	1 mV	
200.00 V	0.01 V	
750.0 V	0.1 V	
Frequency range: 40 Hz-1000 Hz		
<b>DC current</b>		
200.00 mA	0.01 mA	±(1.14 % +14 dig)
10.000 A	1 mA	±(3.57 %+ 14 dig)
Overload protection: mA function: self-healing fuse 400 mA/250 V; Ampere function: 10A/600 V, D5.2*20, fast-acting fuse		
<b>AC current</b>		
200.00 mA	0.01 mA	±(1.43 % +14 dig)
10.000 A	1mA	±(4 % +1 dig)
Frequency range: 40 Hz - 1000 Hz		
Overload protection: mA function: self-healing fuse 400 mA/250 V; Ampere function: 10 A/600 V, D5.2*20, fast-acting fuse		
<b>Resistance</b>		
200.00 Ω	0.01 Ω	±(1.14 % +14 dig)
2.0000 kΩ	0.1 Ω	±(1.14 % +7 dig)
20.000 kΩ	1 Ω	±(1.14 % +4 dig)
200.00 kΩ	10 Ω	
2.0000 MΩ	0.1 kΩ	
20.000 MΩ	1 kΩ	±(1.43 % +4 dig)
100.00 MΩ	0.01 MΩ	±(7.14 % +14 dig)
<b>Capacitance</b>		
20.000 nF	1 pF	±(4.29 % +14 dig)
200.00 nF	10 pF	
2.0000 μF	0.1 nF	
20.000 μF	1 nF	
200.00 μF	10 nF	
2.0000 mF	0.1 uF	
Others	On/Off test	
	Diode test	√(<0-2 V)
	Auto range	√
	TRMS	√

#### Arbitrary Waveform Generator (Optional)

Characteristics	Description	
<b>Waveform Frequency</b>	Sine	0.1 Hz – 25 MHz
	Square	0.1 Hz – 5 MHz
	Ramp	0.1 Hz – 1 MHz
	Pulse	0.1 Hz – 5 MHz
	EXP	0.1 Hz – 5 MHz
<b>Sampling</b>	125 MSa/s	
<b>Amplitude (50 Ω)</b>	0.01V pp - 2.5 Vpp	
<b>DC offset (High Z)</b>	±(2.5 V – Amplitude Vpp/2)	
<b>Frequency Resolution</b>	0.01 %	
<b>Channel</b>	1	
<b>Waveform Depth</b>	8 k	
<b>Vertical Resolution</b>	14 bits	
<b>Output Impedance</b>	50 Ω	

#### Display

Characteristics	Description
Display type	3.5-inch color LCD display
Display resolution	320 horizontal × 240 vertical pixels
Display color	65536 colors
Display Contrast	Adjustable

#### Power supply

Characteristics	Description
Power supply	5 V/DC, 2 A (via USB-C™)
USB-C™ to USB- A cable	Type-C™ to USB 2.0
Power consumption	<5 W
Battery	2x 2200 mAh (3.7 V,18650)

#### Surroundings

Characteristics	Description
Temperature	Working temperature: 0 °C – 40 °C Storage temperature: -20 °C - +60 °C
Relative humidity	≤90 %
Height	Operating: 3,000 meters Non-operating: 15,000 meters
Cooling method	Natural cooling

#### Mechanical specifications

Characteristics	Description
Dimensions (L x H x W)	198 x 96 x 38 mm
Weight	Approx. 0.6 kg (without battery)

#### Software

Characteristics	Description
Supported OS	Windows® XP (Home, Pro, with SP1, SP2, SP3) 32bit, Vista (32 / 64 bit), 7 (32 / 64 bit), 8.0 (32 / 64 bit), 8.1 (32 / 64 bit), 10 (32 / 64 bit)

## CONTENTS

Oscilloscope // USB-C™ to USB-A (data/charging) cable // Probe // Probe adjust //  
 BNC to alligator clip cable // Carrying bag // Multimeter test leads (red & black) //  
 CD-ROM (software + operating instructions + safety sheet + quick guide) // Quick guide // Safety sheet

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE. 2380256\_V1\_0422\_en\_ds 500112779 I1/O1 en