Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: ESYLUX

Supplier's address: -

Model identifier: EO10298981 A

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	NDLS			
Light source cap-type	22 - 36 V DC,					
(or other electric interface)	255 mA CC					
Mains or non-mains:	NMLS	Connected light source (CLS):	Nein			
Colour-tuneable light source:	Nein	Envelope:	-			
High luminance light source:	Nein					
Anti-glare shield:	Nein	Dimmable:	No			
Product parameters						

		i iouuci para				
Parameter		Value	Parameter	Value		
General product parameters:						
01	mption in on- 000 h), rounded est integer	8	Energy efficiency class	E		
indicating if it in a sphere (3	pus flux (φuse), refers to the flux 360º), in a wide in a narrow cone	900 in Sphere (360°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	3 000		
On-mode expressed in W	power (P _{on}), /	7,5	Standby power (P _{sb}), expressed in W and rounded to the second decimal	0,00		
for CLS, expre	ndby power (P _{net}) essed in W and e second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI- values that can be set	80		
Outer dimensions without	Height	25	Spectral power	See image		
	Width	180	distribution in the	in last page		
	Depth	180				
				Seite 1 /		

separate control gear, lighting control parts and non- lighting		range 250 nm to 800 nm, at full-load	
control parts, if any (millimetre)			
Claim of equivalent power ^(a)	-	lf yes, equivalent power (W)	-
		Chromaticity coordinates (x and y)	0,437 0,404
Parameters for LED and OLED ligh	nt sources:	· · ·	
R9 colour rendering index value	-3	Survival factor	-
the lumen maintenance factor	-		
(a), , , , , , , , , , , , , , , , , , ,			

(a)_{'-'} : not applicable;

(b)'-' : not applicable;

