


Product description	M12-A male cable connector, Contacts: 3, shielded, moulded cable, IP67, UL, PUR black, 3 x 0.34 mm <sup>2</sup> , 10 m
Area	M12-A series 763
Part no.	77 3529 0000 50703-1000

### Illustration



### Scale drawing



### Contact arrangement (Plug-in side)



- 1 brown
- 2 not assembled
- 3 blue
- 4 black

Shielded versions; shield = housing

## Technical data

### General features

Part no.	<b>77 3529 0000 50703-1000</b>
	Alternative part no.: 79 3529 35 04
Connector design	male cable connector
Cable length	10 m
Version	male straight
Connector locking system	screw
Termination	moulded cable
Degree of protection	IP67
Cross-sectional area	0.34 mm <sup>2</sup> / AWG 22
Temperature range from/to	-25 °C / 90 °C
Mechanical operation	> 100 Mating cycles
Weight (g)	179.00
Customs tariff number	85444290

### Electrical parameters

Rated voltage	250 V
Rated impulse voltage	2500 V
Rated current (40 °C)	4,0 A
Insulation resistance	≥ 10 <sup>10</sup> Ω
Pollution degree	3
Overvoltage category	II
Insulating material group	II
EMC compliance	shielded
Shield connection	Shield on the threaded ring

# Product data sheet

## Automation technology - sensors and actuators



Product description	M12-A male cable connector, Contacts: 3, shielded, moulded cable, IP67, UL, PUR black, 3 x 0.34 mm <sup>2</sup> , 10 m
Area	M12-A series 763
Part no.	77 3529 0000 50703-1000

### Material

Housing material	PUR
Contact body material	PUR
Contact material	CuZn (brass)
Contact plating	Au (gold)
Locking material	CuZn (brass)
REACH SVHC	CAS 7439-92-1 (Lead)
SCIP number	a2b14bbc-c95d-4a82-99cd-502abed23236

### Authorization/approvals

Approvals	UL
-----------	----

### Classifications

eCl@ss 11.1	27-06-03-11
ETIM 7.0	EC001855

### Declarations of conformity

Low Voltage Directive	2014/35/EU (EN 60529:1991;EN 60204-1:2018)
RoHS Directive	2011/65/EU (EN 50581:2012)

### Cable data - Structure of the cable

Cable diameter	4.6 mm
Cross section	3 x 0.34 mm <sup>2</sup>
Sheath material	PUR
Single-lead insulation	PP9Y halogen-free
Single-lead structure	42 x 0.10 mm
Cable color	black

### Cable data - Electrical properties

Conductor resistance	60 Ω/Km (20°C)
----------------------	----------------

### Cable data - Mechanical properties

Bending radius, fixed cable	≥ 5 x Ø
Bending radius, moving cable	≥ 10 x Ø
Bending cycles	>2 million
Permitted acceleration	5 m/s <sup>2</sup> + 1 m/s <sup>2</sup>
Travel distance, horizontal	5 m/s <sup>2</sup> -> 5 m
Travel distance, vertical	5 m/s <sup>2</sup> -> 2 m

Product description	M12-A male cable connector, Contacts: 3, shielded, moulded cable, IP67, UL, PUR black, 3 x 0.34 mm <sup>2</sup> , 10 m
Area	M12-A series 763
Part no.	77 3529 0000 50703-1000

Travel speed	≤ 200 m/min (5 m horizontal distance)
--------------	---------------------------------------

#### Cable data - Thermal properties

Temperature range cable in move from/to	-25 °C / 90 °C
Temperature range cable fixed from/to	-50 °C / 90 °C

#### Cable data - Other features

Halogen free	Yes
--------------	-----

Product description	<b>M12-A male cable connector, Contacts: 3, shielded, moulded cable, IP67, UL, PUR black, 3 x 0.34 mm<sup>2</sup>, 10 m</b>
Area	<b>M12-A series 763</b>
Part no.	<b>77 3529 0000 50703-1000</b>

### **General Disclaim Notice**

The connector must not be plugged or unplugged under load. Non-observance and improper use can result in personal injury.

The connectors have been developed for applications in plant engineering, control and electrical equipment construction. The user is responsible for checking whether the connectors can also be used in other areas of application.

The user must take suitable safety precautions to ensure that the connector cannot be accidentally disconnected.

Plug connectors with enclosure protection IP 67 and IP 68 are not suitable for use under water. For further information on the IP protection classes, please refer to the "Technical Information" download centre.

To lock the cable connector with the device connector, the threaded ring is tightened "hand-tight" (approx. 60 cNm).