

5V, 12V or 24V Input / 2W / 3kV Functional Isolated / Unregulated 5V Output

DESCRIPTION

The FISM 1769405x41 MagI³C power module series are unregulated, functionally isolated, fully integrated DC/DC converters.

The modules integrate the switching power stage, control circuitry, transformer and input/output capacitors.

The modules require no external components for operation thus reducing design effort and complexity to a minimum.

The FISM family ensures fast time to market and low development costs.

The 1769405x41 series of the FISM family achieves an efficiency of 85% to 86%.


The series is available in an SMT-8 package (13.2 x 11.4 x 7.25)mm.

FEATURES


- 3kV DC functional isolation for 60s
- Nominal input voltage rails: 5V / 12V / 24V
- Output voltage: 5V unregulated
- Low output voltage ripple: Typ. 75mV at full load
- Output voltage accuracy: Typ. -2.5% at full load
- Output power: 2W (0.4A)
- Dynamic power boost up to 0.56A for 0.5s
- Continuous short-circuit protection
- Isolation capacitance of typ. 20pF
- Integrated C_{IN}, C_{OUT} and transformer
- Operating ambient temperature range: -40°C to 105°C
- RoHS & REACH compliant
- Complies with EN55032 (CISPR-32) class B conducted and radiated emissions standard
- UL62368-1 approved

TYPICAL APPLICATIONS

- Data acquisition
- Test and measurement systems
- Interface and microcontroller supplies
- Industrial control



TYPICAL CIRCUIT DIAGRAM



CONTENTS

1	PINOUT	4
2	ORDERING INFORMATION	5
3	PINOUT COMPATIBLE FAMILY MEMBERS	5
4	SALES INFORMATION	5
5	ABSOLUTE MAXIMUM RATINGS	6
6	OPERATING CONDITIONS	6
7	THERMAL SPECIFICATIONS	6
8	ELECTRICAL SPECIFICATIONS	7
9	APPROVALS	8
10	RoHS, REACH	8
11	PACKAGE SPECIFICATIONS	8
12	RELIABILITY	8
13	NOTES	9
14	ISOLATION VOLTAGE	10
	14.1 Dielectric Test Setup (High Pot Test)	10
	14.2 Repeated High-Voltage Isolation Testing	10
15	TYPICAL PERFORMANCE CURVES	11
	15.1 Radiated and Conducted Emissions (With EMI Input Filter)	11
	15.1.1 Radiated Emissions EN55032 (CISPR-32) Class B Complaint Test Setup	11
	15.1.2 Conducted Emissions EN55032 (CISPR-32) Class B Complaint Test Setup	11
	15.1.3 Radiated And Conducted Emissions - 1769405141	12
	15.1.4 Radiated And Conducted Emissions - 1769405241	13
	15.1.5 Radiated And Conducted Emissions - 1769405341	14
	15.2 DC Performance Curves	15
	15.2.1 Efficiency	15
	15.3 Output Power	16
	15.4 Duty Cycle I_{MOC}	17
	15.4.1 Temperature Derating I_{MOC}	18
	15.4.2 Output Voltage Tolerance Envelope	19
16	BLOCK DIAGRAM	20
17	CIRCUIT DESCRIPTION	20
18	PROTECTION FEATURES	21
	18.1 Short-Circuit Protection (SCP)	21
19	DESIGN EXAMPLE	22
	19.1 Layout	22
	19.2 Schematic	23
	19.3 Bill of Materials	24
	19.3.1 Module: 1769405141 (5V Input / 5V Output / 0.4A)	24
	19.3.2 Module: 1769405241 (5V Input / 5V Output / 0.4A)	24
	19.3.3 Module: 1769405341 (5V Input / 5V Output / 0.4A)	25



20 APPLICATION CONSIDERATIONS	26
20.1 Primary Side Parallel Connection	26
20.2 Secondary Side Serial Connection	28
20.3 Generating Complementary Output Voltages	29
20.4 Reverse Polarity Protection	30
21 HANDLING RECOMMENDATIONS	31
21.1 Soldering Profile	31
22 PHYSICAL DIMENSIONS	32
22.1 Component	32
22.2 Recommended Landpattern	32
22.3 Packaging	33
23 DOCUMENT HISTORY	34
24 LIST OF FIGURES	35
25 LIST OF TABLES	36
26 CAUTIONS AND WARNINGS	37
27 IMPORTANT NOTES	38

1 PINOUT




Figure 1: Pinout.

Table 1: Marking description.

MARKING	DESCRIPTION
WE	Würth Elektronik eiSos GmbH & Co. KG
YY	Year
WW	Calendar week
1769405x41	Order code
AA	Input voltage
B	Output voltage
C	Isolation voltage

Table 2: Pin description.

SYMBOL	NUMBER	TYPE	DESCRIPTION
-VIN	1	Power	Input ground pin
+VIN	2	Power	Input voltage pin
-VOUT	4	Power	Output ground pin
+VOUT	5	Power	Output voltage pin
NC	8	—	Not connected

2 ORDERING INFORMATION

Table 3: Ordering information.

ORDER CODE	SPECIFICATIONS	PACKAGE	PACKAGING UNIT
1769405141	5V / 5V version	SMT-8	13" Reel (500 pieces)
1769405241	12V / 5V version	SMT-8	13" Reel (500 pieces)
1769405341	24V / 5V version	SMT-8	13" Reel (500 pieces)

3 PINOUT COMPATIBLE FAMILY MEMBERS

Table 4: Pinout compatible family members.

ORDER CODE	SPECIFICATIONS	PACKAGE	PACKAGING UNIT
1769205141	5V / 5V version	SMT-8	13" Reel (500 pieces)
1769205241	12V / 5V version	SMT-8	13" Reel (500 pieces)
1769205341	24V / 5V version	SMT-8	13" Reel (500 pieces)
176920502	3.3V / 5V version	SMT-8	13" Reel (500 pieces)
176920512	5V / 5V version	SMT-8	13" Reel (500 pieces)
176920522	12V / 5V version	SMT-8	13" Reel (500 pieces)
176881212	5V / 12V version	SMT-8	13" Reel (500 pieces)
176861512	5V / 15V version	SMT-8	13" Reel (500 pieces)

4 SALES INFORMATION

SALES CONTACT
Würth Elektronik eiSos GmbH & Co. KG EMC and Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 7942 945 0 www.we-online.com/powermodules Technical support: powermodules@we-online.com

5 ABSOLUTE MAXIMUM RATINGS

Caution:

Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.

Table 5: Absolute maximum ratings.

SYMBOL	PARAMETER		LIMIT		UNIT
			MIN ⁽¹⁾	MAX ⁽¹⁾	
VIN	Input pin voltage	5V _{IN} / 5V _{OUT} version (1769405141)	-0.4	10	V
		12V _{IN} / 5V _{OUT} version (1769405241)	-0.4	16	V
		24V _{IN} / 5V _{OUT} version (1769405341)	-0.4	50	V
VOUT	Output pin voltage	5V _{IN} / 5V _{OUT} version (1769405141)	-0.7	16	V
		12V _{IN} / 5V _{OUT} version (1769405241)	-0.7	25	V
		24V _{IN} / 5V _{OUT} version (1769405341)	-0.7	16	V
V _{ISO}	Isolation voltage input to output for 1s ⁽⁶⁾		—	4	kV
	Isolation voltage input to output, 100% tested for 60s ⁽⁷⁾		—	3	kV
T _{storage}	Assembled, non-operating storage temperature		-55	125	°C
V _{ESD}	ESD Voltage (HBM), according to EN61000-4-2 ⁽⁴⁾		-4	4	kV

6 OPERATING CONDITIONS

Operating conditions are conditions under which the device is intended to be functional. All values are referenced to GND.

MIN and MAX limits are valid for the recommended ambient temperature range of -40°C to 105°C.

Table 6: Operating conditions.

SYMBOL	PARAMETER	MIN ⁽¹⁾	TYP ⁽³⁾	MAX ⁽¹⁾	UNIT	
VIN	Input Voltage	5V _{IN} / 5V _{OUT} version (1769405141)	4.5	5	5.5	V
		12V _{IN} / 5V _{OUT} version (1769405241)	10.8	12	13.2	V
		24V _{IN} / 5V _{OUT} version (1769405341)	21.6	24	26.4	V
V _{OUT}	Output Voltage	—	5	—	V	
I _{OUT}	Nominal output current ⁽⁵⁾	—	—	0.4	A	
P _{OUT}	Nominal output power (without derating)	—	—	2	W	
C _{OUT_MAX}	Maximal output capacitance	—	—	2400	μF	
T _a	Ambient temperature range	-40	—	105 ⁽²⁾	°C	
T _{JOP}	Junction temperature range	-40	—	125	°C	

7 THERMAL SPECIFICATIONS

Caution:

Exceeding the listed absolute maximum ratings may affect the device negatively and may cause permanent damage.

Table 7: Thermal specifications.

SYMBOL	PARAMETER	TYP ⁽³⁾	UNIT
T _{Case_Max}	Maximum case temperature (top side)	105	°C

8 ELECTRICAL SPECIFICATIONS

Caution:


MIN and MAX limits are valid for the recommended ambient temperature range of -40°C to 105°C. Typical values represent statistically the utmost probable values at the following conditions: $T_A = 25^\circ\text{C}$, unless otherwise noted.

Table 8: Electrical specifications.

SYMBOL	PARAMETER	TEST CONDITIONS	MIN ⁽¹⁾	TYP ⁽³⁾	MAX ⁽¹⁾	UNIT
Output Current						
I_{MOC}	Maximum overload current		—	—	0.56 ⁽⁸⁾	A
Accuracy						
V_{OUT}	Line regulation	per 1.0% change in input voltage ⁽⁹⁾	—	—	1.2	%
	Load Regulation	V_{IN} nominal, $V_{OUT} = 5V$ $I_{OUT} = 0.04A$ to $0.4A$	—	9	15	%
	Output voltage accuracy	V_{IN} nominal, $I_{OUT} = 0.4A$	—	-2.5	—	%
	Output voltage at no load	V_{IN} nominal	—	5.5	—	V
	Output voltage ripple & noise	V_{IN} nominal, $V_{OUT} = 5V$ 20MHz BWL	—	75	—	mV _{PP}
Switching Frequency						
f_{SW}	Switching frequency, internal clock	V_{IN} nominal, $I_{OUT} = 0.4A$	—	300	—	kHz
	Switching frequency, input current	V_{IN} nominal, $I_{OUT} = 0.4A$	—	600 ⁽¹⁰⁾	—	kHz
	Switching frequency, output voltage ripple	V_{IN} nominal, $I_{OUT} = 0.4A$	—	600 ⁽¹⁰⁾	—	kHz
Input Current						
I_{IN}	No load input current (operating, switching)	$V_{IN} = 5V, I_{OUT} = 0A$ (1769405141)	—	8	—	mA
		$V_{IN} = 12V, I_{OUT} = 0A$ (1769405241)	—	4	—	mA
		$V_{IN} = 24V, I_{OUT} = 0A$ (1769405341)	—	5.5	—	mA
Efficiency						
η	Efficiency	$V_{IN} = 5V, I_{OUT} = 0.4A$ (1769405141)	—	85	—	%
		$V_{IN} = 12V, I_{OUT} = 0.4A$ (1769405241)	—	86	—	%
		$V_{IN} = 24V, I_{OUT} = 0.4A$ (1769405341)	—	85	—	%
Isolation Characteristics						
C_{ISO}	Isolation capacitance	100kHz/0.1V	—	20	-	pF
R_{ISO}	Isolation resistance	500VDC	1	—	-	GΩ


9 APPROVALS

Table 9: Approvals.

SYMBOL	STANDARD	DESCRIPTION
	62368-1, 2 nd Edition	Recognized for use as Audio/Video, Information and Communication Technology Equipment, U.S.A. (UL62368-1) and Canada (C22.2 No. 62368-1) E-File: E497615 Applicable for altitudes up to 2000m

10 RoHS, REACH

Table 10: RoHS, REACH.

RoHS directive		Directive 2011/65/EU of the European Parliament and the Council of June 8th, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.
REACH directive		Directive 1907/2006/EU of the European Parliament and the Council of June 1st, 2007 regarding the Registration, Evaluation, Authorization and Restriction of Chemicals (REACH).

11 PACKAGE SPECIFICATIONS

Table 11: Package specifications.

ITEM	PARAMETER	TYP ⁽³⁾	UNIT
Case	UL94V-0 (Refer to UL approval E150608)	—	—
φ (RH)	Maximum storage humidity (see HANDLING RECOMMENDATIONS for soldering requirements)	95	%
Weight		1.3	g
Vibration	MIL-STD-202G: 5g for 1 minute, 120 cycles each of 3 orientation, test from 10Hz-55Hz		
IP	Degree of protection according to IEC/EC 60529	X0	
Washing	Washing compatible with standard industrial water based washers.		

12 RELIABILITY

Table 12: Reliability.

SYMBOL	PARAMETER	TEST CONDITIONS	TYP ⁽³⁾	UNIT
MTBF ⁽¹¹⁾	Mean Time Between Failures	+25°C: Ground Benign	22500 · 10 ³	h
		+100°C: Ground Benign	4800 · 10 ³	h

13 NOTES

- (1)** Min and Max limits are 100% production tested at 25°C. Limits over the operating temperature range are guaranteed through correlation using Statistical Quality Control (SQC) methods.
- (2)** Measured without heatsink, still air. (0 - 20LFM / 0 - 0.1m/s) Test PCB 80mm x 80mm horizontal orientation 35µm copper on top and bottom.
- (3)** Typical numbers are valid at 25°C ambient temperature and represent statistically the utmost probability assuming the Gaussian distribution.
- (4)** The human body model is a 100pF capacitor discharged through a 1.5 kΩ resistor into each pin. Test method is per JESD-22-114.
- (5)** Depending on ambient temperature, see thermal derating diagram ([Output Power](#)).
- (6)** Not production tested. It is a design parameter.
- (7)** Test voltage as defined by the UL62368-1.
- (8)** Overload current, see [Duty Cycle I_{MOC} & Temperature Derating I_{MOC}](#).
- (9)** Within the complete V_{IN} operating range.
- (10)** Due to the converter topology, the external output voltage ripple frequency is twice the internal clock frequency.
- (11)** MIL-HDBK-217F; GB Ground, Benign: Non mobile, temperature and humidity controlled environments readily accessible to maintenance; includes laboratory instruments and test equipment, medical electronic equipment, business and scientific computer complexes, and missiles and support equipment in ground silos; MTBF value is referring to 1769405x41.

14 ISOLATION VOLTAGE

To verify the integrity of the isolation a test voltage is applied for a specified time across a component that is designed to provide electrical isolation. This test is known as 'High Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' or 'Isolation Test Voltage'.

All isolated Power Modules are 100% production tested at their stated isolation voltage. This is 3 kVDC for 60 seconds.

The isolation test voltage indicated in this data sheet is for voltage transient immunity only. It does not allow this part to be used within a safety isolation system.

The module will function properly with several hundreds of volts applied continuously across the isolation barrier, however surrounding components must be individually analyzed to ensure proper insulation. Isolation measures must be taken into account to prevent any user-accessible circuitry from causing harm.

14.1 Dielectric Test Setup (High Pot Test)

Connect all input and output terminals together (see figure below) before connecting the supply voltage. When testing, set the cut-off current to 1mA with a test voltage of 3kVDC and test time of 60s.




Figure 2: Dielectric test setup.

14.2 Repeated High-Voltage Isolation Testing

A repeated high voltage test of a barrier component degrades its isolation capabilities.

The primary and secondary windings within this transformer are enameled (coated) but do not possess additional isolation. Typically, parts can withstand multiples of their stated test voltage and still perform optimally. The magnet wire coating can degrade over time due to chemical reactions that occur at high voltages. We recommend keeping high voltage isolation testing to a minimum to better protect the isolation between the windings. If repeated high voltage isolation testing is required, consider reducing the voltage by a significant amount e.g. 20% from the test voltage stated within the datasheet

These safety concerns are equally applicable to components that utilize functional isolation beyond wire coating (i.e. physical barriers or spacing).

15 TYPICAL PERFORMANCE CURVES

If not otherwise specified, the following conditions apply: $T_A = 25^\circ\text{C}$.

15.1 Radiated and Conducted Emissions (With EMI Input Filter)

The 1769405x41 power modules were tested in several EMC configurations to give more realistic information about implementation in the applications. The test setup is based on CISPR16 with the limit values of CISPR32. All measurements were performed with the layout and components shown in [DESIGN EXAMPLE](#)

15.1.1 Radiated Emissions EN55032 (CISPR-32) Class B Complaint Test Setup

- Measured in a Fully Anechoic Room (FAR) at 3m antenna distance.
- Input wire length: 160cm (80cm horizontal + 80cm vertical)
- Output wire length: 1m

15.1.2 Conducted Emissions EN55032 (CISPR-32) Class B Complaint Test Setup

- Measurement input wire length: 80cm
- Output wire length: 1m

15.1.3 Radiated And Conducted Emissions - 1769405141




Figure 3: 1769405141 radiated EMI nominal V_{IN} / V_{OUT} , $I_{OUT} = 0.4$, with input filter.




Figure 4: 1769405141 conducted EMI nominal V_{IN} / V_{OUT} , $I_{OUT} = 0.4$, with input filter.

15.1.4 Radiated And Conducted Emissions - 1769405241




Figure 5: 1769405241 radiated EMI nominal V_{IN} / V_{OUT} , $I_{OUT} = 0.4$, with input filter.




Figure 6: 1769405241 conducted EMI nominal V_{IN} / V_{OUT} , $I_{OUT} = 0.4$, with input filter.

15.1.5 Radiated And Conducted Emissions - 1769405341




Figure 7: 1769405341 radiated EMI nominal V_{IN} / V_{OUT} , $I_{OUT} = 0.4$, with input filter.




Figure 8: 1769405341 conducted EMI nominal V_{IN} / V_{OUT} , $I_{OUT} = 0.4$, with input filter.

15.2 DC Performance Curves

15.2.1 Efficiency




Figure 9: 1769405x41 efficiency $V_{IN} = \text{Nom.}$

15.3 Output Power




Figure 10: 1769405x41 output power thermal derating nominal V_{IN} , $I_{OUT} = 0.4A$.

15.4 Duty Cycle I_{MOC}




Figure 11: 1769405x41 dynamic power boost nominal V_{IN} , $T_A = 25^\circ\text{C}$.

Note: The overload current of 140% I_{OUT} can be supplied for maximum 0.5s and requires a 3s recovery time until next overload event.

15.4.1 Temperature Derating I_{MOC}




Figure 12: 1769405x41 power boost thermal derating nominal V_{IN}.

Note: Natural convection (0 - 20LFM / 0 - 0.1m/s), output power values are shown as relative power values

15.4.2 Output Voltage Tolerance Envelope




Figure 13: 1769405x41 output voltage tolerance envelope $V_{IN} = 5V/12V/24V$.

16 BLOCK DIAGRAM




Figure 14: 1769405x41 block diagram.

17 CIRCUIT DESCRIPTION

The MagI³C 1769405x41 power modules are based on a push-pull converter. All modules have an integrated IC, rectifying diodes, input and output capacitors and a transformer.

Since there is no feedback path from the output to the input, the duty cycle is fixed at 50% and is independent of the load (zero load to full load). The output voltage is unregulated and defined by the turns ratio of the transformer.

18 PROTECTION FEATURES

18.1 Short-Circuit Protection (SCP)

The modules are continuously output short-circuit protected. The protection is realized via comparing the drain voltages of the MOSFETs to a certain internal reference. During a short circuit situation the output voltage is pulled low. The output voltage recovers to its nominal value after the error is resolved.




Figure 15: 1769405x41 short-circuit protection nominal V_{IN} / V_{OUT} , $I_{OUT} = 0.4$.

19 DESIGN EXAMPLE

The design example shows a possible solution for 5V (1769405141), 12V (1769405241) and 24V (1769405341) to 5V with a max lout of 0.4A. All of the necessary components to fulfill the requirements of the CISPR 32 EMI conducted- and radiated-emissions tests are included in the design example. It passes the conducted emissions class B with 0.8m input- and 1m output lines and passes the radiated emissions class B in a FAR at 3m measurement distance with 0.8m horizontal, 0.8m vertical input- and 1m horizontal outputlines. In the final application filter components may be omitted depending on the requirements.

19.1 Layout




Figure 16: 1769405x41 layout recommendation.

The layout above has been evaluated to provide the optimal performance in terms of transient response, efficiency, ripple and EMI. The design footprint can be reduced at the expense of performance in these parameters. The following recommendation should be followed when designing the layout:

1. The input capacitor should be placed as close as possible to the +VIN and -VIN pins of the device.
2. The output capacitor should be placed as close as possible to the +VOUT and -VOUT pins of the device.
3. The Y-capacitor should be placed as close as possible to the +VIN and -VOUT pins of the device.

19.2 Schematic




Figure 17: 1769405x41 design example schematic.

For optimal EMI performance, one filter capacitor, C1, one filter inductor / common mode choke (cmc), L1, one input capacitor, C2, one output capacitor, C3 and one Y-Cap, C4 are recommended. For optimal electrical performance, one input capacitor C2 and one output capacitor C3 are recommended.

19.3 Bill of Materials

19.3.1 Module: 1769405141 (5V Input / 5V Output / 0.4A)

Table 13: 1769405141 design example bill of materials.

DESIGNATOR	DESCRIPTION	FUNCTION	QUANTITY	ORDER CODE	MANUFACTURER
U1	Magl ³ C Power Module	Power supply	1	1769405141	WE
L1	Filter inductor, 6.8μH, PD2 family, I _{SAT} = 2.1A, I _R = 1.54A	Input Filter	1	744773068	WE
C1	Ceramic chip capacitor 4.7μF/10V X7R, 1210	Input Filter	1	885012209004	WE
C2	Ceramic chip capacitor 4.7μF/10V X7R, 1210	Input Filter / Electrical Performance	1	885012209004	WE
C3	Ceramic chip capacitor 10μF/16V X7R, 1210	Output Filter / Electrical Performance	1	885012209014	WE
C4	Ceramic chip capacitor 470pF/3kV Impulse 1808 X7R	Y-Cap	1	885342210003	WE

19.3.2 Module: 1769405241 (5V Input / 5V Output / 0.4A)

Table 14: 1769405241 design example bill of materials.

DESIGNATOR	DESCRIPTION	FUNCTION	QUANTITY	ORDER CODE	MANUFACTURER
U1	Magl ³ C Power Module	Power supply	1	1769405241	WE
L1	Filter inductor (cmc), 10μH, SL2 family, I _R = 1.6A	Input Filter	1	744226S	WE
C1	Ceramic chip capacitor 4.7μF/16V X7R, 1210	Input Filter	1	885012209013	WE
C2	Ceramic chip capacitor 4.7μF/16V X7R, 1210	Input Filter / Electrical Performance	1	885012209013	WE
C3	Ceramic chip capacitor 10μF/16V X7R, 1210	Output Filter / Electrical Performance	1	885012209014	WE
C4	Ceramic chip capacitor 470pF/3kV Impulse 1808 X7R	Y-Cap	1	885342210003	WE

19.3.3 Module: 1769405341 (5V Input / 5V Output / 0.4A)

Table 15: 1769405341 design example bill of materials.

DESIGNATOR	DESCRIPTION	FUNCTION	QUANTITY	ORDER CODE	MANUFACTURER
U1	Magl ³ C Power Module	Power supply	1	1769405341	WE
L1	Filter inductor (cmc), 10 μ H, SL2 family, $I_R = 1.6A$	Input Filter	1	744226S	WE
C1	Ceramic chip capacitor 4.7 μ F/50V X7R, 1210	Input Filter	1	885012209048	WE
C2	Ceramic chip capacitor 4.7 μ F/50V X7R, 1210	Input Filter / Electrical Performance	1	885012209048	WE
C3	Ceramic chip capacitor 10 μ F/16V X7R, 1210	Output Filter / Electrical Performance	1	885012209014	WE
C4	Ceramic chip capacitor 470pF/3kV Impulse 1808 X7R	Y-Cap	1	885342210003	WE

20 APPLICATION CONSIDERATIONS

20.1 Primary Side Parallel Connection

A standard industrial configuration is, that the power modules are supplied by a dc bus voltage. Multiple 1769405x41 can be connected to one dc bus as shown in the figure below.

The outputs must not be connected in parallel to each other and could have individual voltages V_{OUT1} and V_{OUT2} . For serial connection of the output see also '[Secondary Side Serial Connection](#)'.




Figure 18: Primary side parallel connection.

In case of using long supply lines or different wire length for each 1769405x41 it is recommended to decouple each power module with an additional LC filter (see schematic below). The decoupling LC filter is also recommended if the supplying dc bus has a high impedance so that high voltage swings at the input of each power module might be present.




Figure 19: Decoupling for primary side parallel connection.

As a starting point for the decoupling filters, use the values of the reference filters - see also '[Radiated And Conducted Emissions \(With Input Filter\)](#)'. The final appropriate filter for the application has then to be evaluated under operation in the target application by checking e.g. the change of the input ripple voltage.

20.2 Secondary Side Serial Connection

To generate a higher output voltage it is possible to put the outputs of the 1769405x41 in series. It is common practice to connect an additional capacitor between the +VOUT and -VOUT.




Figure 20: Primary side serial connection.

In case of using long supply lines or different line length for each 1769405x41 it is recommended to decouple each power module with an additional LC filter. The decoupling LC filter is also recommended if the supplying dc bus has a high impedance so that high voltage swings at the input of each power module could be present. As initial values, the EMI filter shown for every part number can be used. See also '[Primary Side Parallel Connection](#)'.

20.3 Generating Complementary Output Voltages

Another common requirement in industrial applications is to provide a complementary voltage ($\pm 5V$). This can be easily implemented by using two 1769405x41 modules according to the schematic below. It is a common practice to connect an additional capacitor across each output voltage.




Figure 21: Generating complementary output voltages.

For using long supply lines or different line length for each 1769405x41 it is recommended to decouple each power module with an additional LC- filter. The decoupling LC-filter is also recommended if the supplying dc bus has a high impedance so that high voltage swings at the input of each power module could be present. As initial values, the EMI filter shown for every part number can be used. See also '[Primary Side Parallel Connection](#)'.

20.4 Reverse Polarity Protection

A simple way of creating an input reverse polarity protection is to place a diode in series with the positive input line. Due to the forward voltage drop of the diode the application efficiency drops.




Figure 22: Reverse polarity protection.

21 HANDLING RECOMMENDATIONS

1. The power module is classified as MSL1 (JEDEC Moisture Sensivity Level 1) and doesn't requires special handling due to moisture sensitivity (JEDEC J-STD033).
2. Parts have unlimited floor life according to JEDEC J-STD033.
3. Maximum numbers of reflow cycles is three.
4. For minimum risk, solder the module in the last reflow cycle of the PCB production.
5. The component lead material is copper (Cu) and the lead finish is ENEPIG (NiPdAu).
6. For solder paste use a standard SAC Alloy such as SAC 305, type 3 or higher.
7. The profile below is valid for convection reflow only
8. Other soldering methods (e.g. vapor phase) are not verified and have to be validated by the customer at their own risk

21.1 Soldering Profile

Table 16: Reflow solder profile.

Profile Feature	Symbol	Value
Preheat temperature minimum	T_{s_min}	150°C
Preheat temperature maximum	T_{s_max}	180°C
Preheat time from T_{s_min} to T_{s_max}	t_s	60-90 seconds
Liquidous temperature	T_L	217°C
Time maintained above T_L	t_L	60-90 seconds
Classification temperature	T_C	245°C
Peak package body temperature	T_P	$T_P \leq T_C$
Time within $T_C - 5^\circ\text{C}$ and T_C	t_p	$t_p \leq 20$ seconds
Ramp-up Rate (T_L to T_P)		3°C/second maximum
Ramp-down rate (T_P to T_L)		3°C/second maximum
Time 25°C to peak temperature		8 minutes maximum

Please refer to JEDEC J-STD020 for further information pertaining to reflow soldering of electronic components.




Figure 23: Solder profile.

22 PHYSICAL DIMENSIONS

22.1 Component




Figure 24: Physical dimensions.

All dimensions in mm Tolerance: xx.x = ±0.5mm ; xx.xx = ±0.25mm unless otherwise noted

22.2 Recommended Landpattern




Figure 25: Recommended landpattern dimensions.

22.3 Packaging

Tape and Reel (mm)




Figure 26: Packaging dimensions.

Table 17: Tape dimensions.

A0	B0	D0 / D1	E1	E2	K0	P0	P1	P2	T	T1	T2	W
±0.10	±0.10	±0.10	±0.10	±0.10	±0.10	±0.10	±0.10	±0.05			±0.10	±0.10
11.70	13.10	1.50	1.75	22.25	7.50	4.00	16.00	2.00	0.50	0.35	8.00	24.00

Tape material is polystyrene

Table 18: Reel dimensions.

A	B	C	D	N	W1	W2	W3
±2.0	±0.30	±0.20	±0.50	±1.00	+1.00 -0.50	±2.00	+1.00 -0.50
330.00	2.30	13.00	21.00	100.00	24.5	28.50	24.50

23 DOCUMENT HISTORY

Table 19: Document history.

Revision	Date	Description	Comment
1.0	April 2022	Initial release of data sheet	
2.0	July 2023	Major change	To improve the processability, Würth Elektronik has expanded the reflow solder profile to align with the JEDEC J-STD020E industry standard for reflow soldering. As a datasheet information amendment, Würth Elektronik has changed the specified switching frequency to create a better understanding between the internal and external switching frequency of the topology and to justify the shown EMC diagrams. This is a datasheet correction only. There will be no change in form, fit, function, quality or reliability of the product. All date codes will be affected by this change.

24 LIST OF FIGURES

1	Pinout.	4
2	Dielectric test setup.	10
3	1769405141 radiated EMI.	12
4	1769405141 conducted EMI.	12
5	1769405241 radiated EMI.	13
6	1769405241 conducted EMI.	13
7	1769405341 radiated EMI.	14
8	1769405341 conducted EMI.	14
9	Efficiency $V_{IN} = \text{Nom}$	15
10	Output power thermal derating nominal V_{IN} , $I_{OUT} = 0.4A$	16
11	Dynamic power boost nominal V_{IN} , $T_A = 25^\circ C$	17
12	Power boost thermal derating nominal V_{IN}	18
13	Output voltage tolerance envelope $V_{IN} = 5V/12V/24V$	19
14	1769405x41 Block diagram	20
15	Short-circuit protection.	21
16	Layout recommendation.	22
17	Design example schematic.	23
18	Primary side parallel connection.	26
19	Decoupling for primary side parallel connection.	27
20	Primary side serial connection.	28
21	Generating complementary output voltages.	29
22	Reverse polarity protection.	30
23	Solder profile.	31
24	Physical dimensions.	32
25	Recommended landpattern dimensions.	32
26	Packaging dimensions.	33

25 LIST OF TABLES

1	Marking description.	4
2	Pin description.	4
3	Ordering information.	5
4	Pinout compatible family members.	5
5	Absolute maximum rating.	6
6	Operating conditions.	6
7	Thermal specifications.	6
8	Electrical specifications.	7
9	Approvals.	8
10	RoHS, REACH.	8
11	Package specifications.	8
12	Reliability.	8
13	1769405141 design example bill Of materials.	24
14	1769405241 design example bill of materials.	24
15	1769405341 design example bill of materials.	25
16	Reflow solder profile.	31
17	Tape dimensions.	33
18	Reel dimensions.	33
19	Document history.	34

26 CAUTIONS AND WARNINGS

The following conditions apply to all goods within the product series of MagI³C of Würth Elektronik eiSos GmbH & Co. KG:

General:

- All recommendations according to the general technical specifications of the data-sheet have to be complied with.
- The usage and operation of the product within ambient conditions which probably alloy or harm the component surface has to be avoided.
- The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply for customer specific products
- Residual washing varnish agent that is used during the production to clean the application might change the characteristics of the body, pins or termination. The washing varnish agent could have a negative effect on the long term function of the product. Direct mechanical impact to the product shall be prevented as the material of the body, pins or termination could flake or in the worst case it could break. As these devices are sensitive to electrostatic discharge customer shall follow proper IC Handling Procedures.
- Customer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of Würth Elektronik eiSos GmbH & Co. KG components in its applications, notwithstanding any applications-related information or support that may be provided by Würth Elektronik eiSos GmbH & Co. KG.
- Customer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences lessen the likelihood of failures that might cause harm and take appropriate remedial actions
- Customer will fully indemnify Würth Elektronik eiSos and its representatives against any damages arising out of the use of any Würth Elektronik eiSos GmbH & Co. KG components in safety-critical applications

Product specific:

Follow all instructions mentioned in the datasheet, especially:

- The solder profile has to comply with the technical reflow or wave soldering specification, otherwise this will void the warranty.
- All products are supposed to be used before the end of the period of 12 months based on the product date-code.
- Violation of the technical product specifications such as exceeding the absolute maximum ratings will void the warranty.
- It is also recommended to return the body to the original moisture proof bag and reseal the moisture proof bag again.
- ESD prevention methods need to be followed for manual handling and processing by machinery.

Disclaimer:

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co. KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. Würth Elektronik eiSos GmbH & Co. KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance. These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

27 IMPORTANT NOTES

General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not. Accordingly, the customer is cautioned to verify that the datasheet is current before placing orders.

Customer Responsibility Related to Specific, in Particular Safety-Relevant, Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component.

Best Care and Attention

Any product-specific notes, warnings and cautions must be strictly observed. Any disregard will result in the loss of warranty.

Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard we inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG. Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.