

Linemaster Switch Corporation

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service_266@linemaster.com Web site: www.linemaster.com

Item # 491-SC36, Compact Foot Switch



Compact Foot Switch

Compact in size and light in weight. Built for long life, the strong steel housing is painted black with nonskid base pad. The twin consists of two single models mounted on a single cast aluminum base with a divider bar between pedals which helps prevent accidental operation of both pedals at one time.

SPECIFICATIONS

Description	Momentary
Circuit	SPDT Wired N.O.
Form	A
Electrical Rating	10 A 125-250 VAC 1/2 H.P. 125-250 VAC
Standard	EN 60529 Degree of Protection IP20
Size	2 7/8 x 2 1/2 x 1 1/8 Inch
Weight Approx.	7 Oz.
Note	Supplied with 6 ft. 16/3 cord without plug. Green lead grounded, MP - Supplied with integral mounting plate.
